# EVU-3-32-TP-R

#### Three- phase connection unit with 3 x 32amp TPN Type A RCBOs

The **EVU-3-32-TP-R** from matt:e is simple single dedicated connection unit with built in **O-PEN** technology, which allows for the connection of 3 x 32 amp TPN EV charge points to the existing PME earthing facility.

The unit incorporates a 5 pole isolator with built-in UV release that disconnects all poles including CPC in the event of a fault, manually resettable in line with BS: 7671, 2018 Amendment 1 2020 Regulation 722.411.4.1 (iii)

The **O-PEN** technology does not require earth rods or measuring electrodes to function correctly.



#### **Product Features**

- Built in O-PEN technology
- Standard mild steel IP4X enclosure
- NO EARTH ELECTRODES REQUIRED
- Phase loss protection
- Built in 5 pole mains isolator with manually resettable UV release.
- Standard 1 Year parts warranty
- Simple wire in wire out connection
- With 3 x 32amp TPN Type A RCBOs
- Designed and Built in the UK


...Simplifying EV connection






## **EVU-3-32-TP-R**

## **Dimensions and Specifications**





Description	Dedicated EV connection centre
Input Volts	Nominal input voltage three-phase 400V 50Hz
Max Load	32 amps per load
Cable Entry Facility	Top and bottom
Terminal Capacity	Supply 50.0 mm2
	Load 25.0 mm2
Dimensions ( H x W x D )	550mm x 360mm x 140mm
Weight	Approximately 10kG
Enclosure	Mild Steel Powder Coated
Ingress Protection	IP4X
Warranty	The matt:e <i>EVU-3-32-TP-R</i> is guaranteed for a period of 1 year from the date of purchase. This warranty is limited to the replacement of faulty components only.

### ...Simplifying EV connection



