

Product information

79 02 125 S1

Precision Electronics Diagonal Cutter

E.g. for opening plastic cable connectors

DIN ISO 9654



- Round head
- All edges on the head are rounded - reduces the risk of damage to the insulation when making corrections to cable harnesses.
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened




General

| | |
|-------------|----------------------------|
| Article No. | 79 02 125 S1 |
| EAN | 4003773071808 |
| Pliers | burnished |
| Head | polished |
| Handles | with multi-component grips |
| weight | 59 g |
| Dimensions | 125 x 59 x 19 mm |
| Standard | DIN ISO 9654 |
| Reach | no |
| RohS | no |

Technical details

| | |
|--|----------------|
| Style | 0 |
| Cutting capacities medium hard wire (diameter) | Ø 1.3 mm |
| Cutting capacities hard wire (diameter) | Ø 0.7 mm |
| Cutting capacities soft wire (diameter) | Ø 0.2 – 1.7 mm |
| | 10 mm |
| | 6.5 mm |
| Head width (A) | 11 mm |

Technical details



Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC000165 |
| ETIM 6.0 | EC000165 |
| proficl@ss 6.0 | AAA949c004 |

technical change and errors excepted

