

# Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 12

## LOCTITE SI 5331 WH TB100ML EN/DE

SDS No. : 152750 V004.0 Revision: 20.11.2018 printing date: 16.03.2019 Replaces version from: 10.05.2017

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1. Product identifier** LOCTITE SI 5331 WH TB100ML EN/DE
- **1.2. Relevant identified uses of the substance or mixture and uses advised against** Intended use: Silicone sealant
- **1.3. Details of the supplier of the safety data sheet** Henkel Ltd

Adhesives Wood Lane End HP2 4RQ Hemel Hempstead

Great Britain

Phone:	+44 (1442) 278000
Fax-no.:	+44 (1442) 278071

ua-productsafety.uk@henkel.com

## **1.4. Emergency telephone number**

24 Hours Emergency Tel: +44 (0)1442 278497

## **SECTION 2: Hazards identification**

### 2.1. Classification of the substance or mixture

Classi	fic	cat	ioı	n (CLI	P):	
~ 1						

Skin irritation H315 Causes skin irritation. Serious eye damage H318 Causes serious eye damage.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Contains

Methyltriacetoxysilane

Signal word:

Danger

Category 2

Category 1

Hazard statement:	H315 Causes skin irritation. H318 Causes serious eye damage.
Precautionary statement: Prevention	P280 Wear eye protection/face protection.
Precautionary statement: Response	P302+P352 IF ON SKIN: Wash with plenty of soap and water. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

#### 2.3. Other hazards

None if used properly. Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria. Evolves acetic acid during cure.

## **SECTION 3: Composition/information on ingredients**

### 3.2. Mixtures

#### General chemical description:

Acetoxy curing silicone

### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Quartz (SiO2), <1% respirable 14808-60-7	238-878-4	5- < 10 %	
Methyltriacetoxysilane 4253-34-3	224-221-9 01-2119962266-32	1-< 5%	Acute Tox. 4; Oral H302 Skin Corr. 1B H314

For full text of the H - statements and other abbreviations see section 16 "Other information". Substances without classification may have community workplace exposure limits available.

## **SECTION 4: First aid measures**

#### 4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact: Rinse with running water and soap. Obtain medical attention if irritation persists.

Eye contact: Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion: Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

## 4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

After eye contact: Corrosive, may cause permanent damage to eyes (impairment of vision).

**4.3. Indication of any immediate medical attention and special treatment needed** See section: Description of first aid measures

## **SECTION 5: Firefighting measures**

### 5.1. Extinguishing media

Suitable extinguishing media: Carbon dioxide, foam, powder Fine water spray

Extinguishing media which must not be used for safety reasons: None known

#### 5.2. Special hazards arising from the substance or mixture

Formaldehyde carbon oxides. Silica fume

#### **5.3. Advice for firefighters**

Wear self-contained breathing apparatus.

### Additional information:

In case of fire, keep containers cool with water spray.

### **SECTION 6: Accidental release measures**

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes. Ensure adequate ventilation. Wear protective equipment.

#### 6.2. Environmental precautions

Do not let product enter drains.

#### 6.3. Methods and material for containment and cleaning up

Scrape up as much material as possible. Ensure adequate ventilation. Store in a partly filled, closed container until disposal. Dispose of contaminated material as waste according to Section 13.

#### 6.4. Reference to other sections

See advice in section 8

### **SECTION 7: Handling and storage**

### 7.1. Precautions for safe handling

Vapours should be extracted to avoid inhalation. Ensure that workrooms are adequately ventilated. Avoid skin and eye contact. See advice in section 8

#### Hygiene measures:

Good industrial hygiene practices should be observed. Do not eat, drink or smoke while working. Take off contaminated clothing and wash before reuse.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container protected against moisture. Store in a cool, well-ventilated place. Refer to Technical Data Sheet

### 7.3. Specific end use(s)

Silicone sealant

## **SECTION 8: Exposure controls/personal protection**

## 8.1. Control parameters

## **Occupational Exposure Limits**

### Valid for

Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Quartz (SiO2) 14808-60-7 [SILICA, RESPIRABLE CRYSTALLINE]		0,1	Time Weighted Average (TWA):		EH40 WEL
Quartz (SiO2) 14808-60-7 [RESPIRABLE CRYSTALLINE SILICA DUST, RESPIRABLE FRACTION]		0,1	Time Weighted Average (TWA):		EU OELIII
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative	ECTLV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	Indicative	ECTLV

## **Occupational Exposure Limits**

### Valid for

Ireland

Ingredient [Regulated substance]	ррт	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, TOTAL INHALABLE DUST]		6	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		IR_OEL
Quartz (SiO2) 14808-60-7 [QUARTZ, RESPIRABLE DUST (SEE CRYSTALLINE SILICA)]		0,1	Time Weighted Average (TWA):		IR_OEL
Quartz (SiO2) 14808-60-7 [RESPIRABLE CRYSTALLINE SILICA DUST, RESPIRABLE FRACTION]		0,1	Time Weighted Average (TWA):		EU OELIII
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	15	37	Short Term Exposure Limit (STEL):	Indicative OELV	IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative	ECTLV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	Indicative	ECTLV

## Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
		periou	mg/l	ppm	mg/kg	others	
Methylsilanetriyl triacetate 4253-34-3	aqua (freshwater)		1,0 mg/l				
Methylsilanetriyl triacetate 4253-34-3	aqua (marine water)		0,1 mg/l				
Methylsilanetriyl triacetate 4253-34-3	aqua (intermittent releases)		10 mg/l				
Methylsilanetriyl triacetate 4253-34-3	sediment (freshwater)				0,80 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	sediment (marine water)				0,08 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	Soil				0,13 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	sewage treatment plant (STP)		> 10 mg/l				

### Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Methylsilanetriyl triacetate 4253-34-3	Workers	inhalation	Long term exposure - systemic effects		25 mg/m3	
Methylsilanetriyl triacetate 4253-34-3	Workers	inhalation	Acute/short term exposure - systemic effects		25 mg/m3	
Methylsilanetriyl triacetate 4253-34-3	Workers	dermal	Long term exposure - systemic effects		14,5 mg/kg	
Methylsilanetriyl triacetate 4253-34-3	Workers	dermal	Acute/short term exposure - systemic effects		14,5 mg/kg	
Methylsilanetriyl triacetate 4253-34-3	General population	inhalation	Long term exposure - local effects		5,1 mg/m3	
Methylsilanetriyl triacetate 4253-34-3	General population	inhalation	Acute/short term exposure - local effects		5,1 mg/m3	
Methylsilanetriyl triacetate 4253-34-3	General population	dermal	Long term exposure - systemic effects		7,2 mg/kg	
Methylsilanetriyl triacetate 4253-34-3	General population	dermal	Acute/short term exposure - systemic effects		7,2 mg/kg	
Methylsilanetriyl triacetate 4253-34-3	General population	oral	Long term exposure - systemic effects		1 mg/kg	
Methylsilanetriyl triacetate 4253-34-3	General population	oral	Acute/short term exposure - systemic effects		1 mg/kg	

# **Biological Exposure Indices:**

None

## 8.2. Exposure controls:

Engineering controls: Ensure good ventilation/extraction. Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387) This recommendation should be matched to local conditions.

Hand protection: Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): nitrile rubber (NBR; >= 0.4 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes p as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Explosive properties

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing. Protective eye equipment should conform to EN166.

Skin protection: Wear protective equipment. Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

## **SECTION 9: Physical and chemical properties**

No data available / Not applicable

# 9.1. Information on basic physical and chemical properties

**	
white	
Odor Acetic acid	
Odour threshold No data availa	able / Not applicable
pH Not applicable	e
Melting point No data availa	able / Not applicable
Solidification temperature No data availa	able / Not applicable
Initial boiling point Not determine	ed
Flash point $> 100 \degree C (> 2)$	12 °F)
Evaporation rate No data availa	able / Not applicable
Flammability No data availa	able / Not applicable
Explosive limits No data availa	able / Not applicable
Vapour pressure Not determine	ed
Relative vapour density: Heavier than	air
Density 1,14 g/cm3	
0	
Bulk density No data availa	able / Not applicable
Solubility No data availa	able / Not applicable
Solubility (qualitative) Polymerises in	n presence of water.
Partition coefficient: n-octanol/water No data availa	able / Not applicable
Auto-ignition temperature No data availa	able / Not applicable
Decomposition temperature No data availa	able / Not applicable
Viscosity No data availa	able / Not applicable
Viscosity (kinematic) No data availa	able / Not applicable

#### Oxidising properties

No data available / Not applicable

### 9.2. Other information

No data available / Not applicable

## **SECTION 10: Stability and reactivity**

### 10.1. Reactivity

Strong oxidizing agents. Polymerises in presence of water.

### 10.2. Chemical stability

Stable under recommended storage conditions.

#### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

No decomposition if used according to specifications.

### **10.5. Incompatible materials**

See section reactivity.

### 10.6. Hazardous decomposition products

At higher temperatures (>150C) may release formaldehyde (traces). Evolves acetic acid during cure.

## **SECTION 11: Toxicological information**

#### General toxicological information:

Acetic acid is liberated slowly upon contact with moisture. Acetic acid released during polymerisation of acetoxy curing RTV silicones is irritating to the eyes

#### 11.1. Information on toxicological effects

#### Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances	Value	Value	Species	Method
CAS-No.	type			
Quartz (SiO2), <1% respirable 14808-60-7	LD50	> 2.000 mg/kg	not specified	not specified
Methyltriacetoxysilane 4253-34-3	LD50	1.600 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)

#### Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Quartz (SiO2), <1%	LD50	> 2.000 mg/kg	not specified	not specified
respirable				
14808-60-7				

### Acute inhalative toxicity:

No data available.

#### Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	corrosive	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

### Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	Category 1 (irreversible effects on the eye)		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

### Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Methyltriacetoxysilane 4253-34-3	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

### Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Methyltriacetoxysilane 4253-34-3	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Methyltriacetoxysilane 4253-34-3	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)

### Carcinogenicity

No data available.

### **Reproductive toxicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Methyltriacetoxysilane 4253-34-3	NOAEL P >= 1.000 mg/kg NOAEL F1 >= 1.000 mg/kg	screening	oral: gavage	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)

### STOT-single exposure:

No data available.

### STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Methyltriacetoxysilane 4253-34-3	NOAEL 50 mg/kg	oral: gavage	28-51 d daily	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)

### Aspiration hazard:

No data available.

## **SECTION 12: Ecological information**

#### General ecological information:

Do not empty into drains / surface water / ground water.

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

In the cured state contribution of this product to Environmental Hazards is insignificant in comparison to articles in which it is used.

### 12.1. Toxicity

### Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances	Value	Value	Exposure time	Species	Method
CAS-No.	type				
Quartz (SiO2), <1% respirable 14808-60-7	LC50	> 1.000 mg/l			OECD Guideline 203 (Fish, Acute Toxicity Test)
Methyltriacetoxysilane 4253-34-3	LC50	> 110 mg/l	96 h	5 5	OECD Guideline 203 (Fish, Acute Toxicity Test)

### Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Quartz (SiO2), <1% respirable 14808-60-7	EC50	> 1.000 mg/l			OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

### Chronic toxicity to aquatic invertebrates

No data available.

### Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances	Value	Value	Exposure time	Species	Method
CAS-No.	type				
Quartz (SiO2), <1% respirable	EC50	> 1.000 mg/l			OECD Guideline 201 (Alga,
14808-60-7					Growth Inhibition Test)

#### Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances	Value	Value	Exposure time	Species	Method
CAS-No.	type				
Quartz (SiO2), <1% respirable	EC0	> 1.000 mg/l			not specified
14808-60-7		-			-

### 12.2. Persistence and degradability

The product is not biodegradable.

No substance data available.

#### 12.3. Bioaccumulative potential

No data available.

No substance data available.

#### 12.4. Mobility in soil

Cured adhesives are immobile.

No substance data available.

### 12.5. Results of PBT and vPvB assessment

Hazardous substances	PBT / vPvB
CAS-No.	
Quartz (SiO2), <1% respirable	According to Annex XIII of regulation (EC) 1907/2006 a PBT and vPvB assessment shall not
14808-60-7	be conducted for inorganic substances.
Methyltriacetoxysilane	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very
4253-34-3	Bioaccumulative (vPvB) criteria.

### 12.6. Other adverse effects

No data available.

## **SECTION 13: Disposal considerations**

#### 13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

	SECTION 14: Transport information
14.1.	UN number
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.2.	UN proper shipping name
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.3.	Transport hazard class(es)
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.4.	Packing group
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.5.	Environmental hazards
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.6.	Special precautions for user
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.7.	Transport in bulk according to Annex II of Marpol and the IBC Code
	not applicable

# **SECTION 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture** VOC content <5 % (2010/75/EC)

### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

### **SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text

of all abbreviations indicated by codes in this safety data sheet are as follows:

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

#### **Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.