



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

SAFETY DATA SHEET

First Acrylic

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name

First Acrylic

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Art supplies and hobby preparations

Uses advised against

None known.

1.3. Details of the supplier of the safety data sheet

Company and address

Daler-Rowney Ltd.

Peacock Lane Bracknell

RG12 8ST Bracknell

United Kingdom

+44 1344 461 156 (0730 – 1600 GMT)

www.daler-rowney.com

Contact person

Research and Development

Revision

09/10/2024

SDS Version

1.0

1.4. Emergency telephone number

Healthcare professionals: Dial 0344 892 0111 to reach The National Poisons Information Service (NPIS) (24 hour service)

General public:

England - Dial 111 to reach NHS 111 (24 hour service)

Scotland - Dial 112 to reach NHS 24 (24 hour service)

Wales - Dial 111 or 0845 4647 to reach NHS Direct (24 hour service)

See section 4 "First aid measures".

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Not classified according to Regulation (EC) No. 1272/2008 (CLP) as retained and amended in UK law.

2.2. Label elements

Hazard pictogram(s)

Not applicable.

Signal word

Not applicable.

Hazard statement(s)

Not applicable.



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

Precautionary statement(s)

General

-

Prevention

-

Response

-

Storage

-

Disposal

-

Hazardous substances

Dolomite

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]

2-phenoxyethanol

2-aminoethanol;ethanolamine

Sodium p-chloro-m-cresolate

Additional labelling

Not applicable.

2.3. Other hazards

Additional warnings

This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.

This product does not contain any substances considered to be endocrine disruptors in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2023/707.

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable. This product is a mixture.

3.2. Mixtures

Product/substance	Identifiers	% w/w	Classification	Note
2-aminoethanol;ethanolamine	CAS No.: 141-43-5 EC No.: 205-483-3 UK-REACH: Index No.: 603-030-00-8	<0.25%	Acute Tox. 4, H302 Acute Tox. 4, H312 Skin Corr. 1B, H314 Eye Dam. 1, H318 Acute Tox. 4, H332 STOT SE 3, H335 Aquatic Chronic 3, H412	[1]

See full text of H-phrases in section 16. Occupational exposure limits are listed in section 8, if these are available.

Other information

[1] European occupational exposure limit.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

In the case of accident: Contact a doctor or casualty department – take the label or this safety data sheet.

Contact a doctor if in doubt about the injured person's condition or if the symptoms persist. Never give an



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

unconscious person water or other drink.

Inhalation

In case of discomfort: bring the person into fresh air.

Skin contact

Upon irritation: rinse with water. In the event of continued irritation, seek medical assistance.

Eye contact

Rinse gently with lukewarm water. Remove any contact lenses if this is easy to do. Continue rinsing. In case of persistent eye irritation or discomfort: Seek medical help.

Ingestion

Rinse and flush mouth thoroughly and consume large quantities of water. In case of continued discomfort: seek medical assistance and bring this safety data sheet.

Burns

Not applicable.

4.2. Most important symptoms and effects, both acute and delayed

None known.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

Information to medics

Bring this safety data sheet or the label from this product.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media: Alcohol-resistant foam, carbon dioxide, powder, water mist.

Unsuitable extinguishing media: Waterjets should not be used, since they can spread the fire.

5.2. Special hazards arising from the substance or mixture

Fire will result in dense smoke. Exposure to combustion products may harm your health. Closed containers, which are exposed to fire, should be cooled with water. Do not allow fire-extinguishing water to enter the sewage system and nearby surface waters.

5.3. Advice for firefighters

Fire fighters should wear appropriate personal protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation, especially in confined areas.

Contaminated areas may be slippery.

6.2. Environmental precautions

Avoid discharge to lakes, streams, sewers, etc.

Keep unauthorized persons away from the spill

6.3. Methods and material for containment and cleaning up

Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations.

Wherever possible cleaning should be performed with normal cleaning agents. Avoid use of solvents.

6.4. Reference to other sections

See section 13 "Disposal considerations" on handling of waste.

See section 8 "Exposure controls/personal protection" for protective measures.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Smoking, drinking and consumption of food is not allowed in the work area.



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

See section 8 "Exposure controls/personal protection" for information on personal protection.

7.2. Conditions for safe storage, including any incompatibilities

No special conditions required.

Recommended storage material

Always store in containers of the same material as the original container.

Storage conditions

No specific requirements

Incompatible materials

No specific requirements

7.3. Specific end use(s)

This product should only be used for applications quoted in section 1.2.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]

Long term exposure limit (8 hours) (mg/m^3): 10(inhalable)/4(respirable)

2-aminoethanol;ethanolamine

Long term exposure limit (8 hours) (ppm): 1

Long term exposure limit (8 hours) (mg/m^3): 2,5

Short term exposure limit (15 minutes) (ppm): 3

Short term exposure limit (15 minutes) (mg/m^3): 7,6

Annotations:

Sk = Can be absorbed through the skin and lead to systemic toxicity.

The Control of Substances Hazardous to Health Regulations 2002. SI 2002/2677 The Stationery Office 2002.
EH40/2005 Workplace exposure limits (Fourth Edition 2020).

DNEL

2-aminoethanol;ethanolamine

Duration:	Route of exposure:	DNEL:
Long term – Systemic effects - General population	Dermal	1.5 mg/kg bw/day
Long term – Systemic effects - Workers	Dermal	3 mg/kg bw/day
Long term – Local effects - General population	Inhalation	280 $\mu\text{g}/\text{m}^3$
Long term – Local effects - Workers	Inhalation	510 $\mu\text{g}/\text{m}^3$
Long term – Systemic effects - General population	Inhalation	180 $\mu\text{g}/\text{m}^3$
Long term – Systemic effects - Workers	Inhalation	1 mg/ m^3
Long term – Systemic effects - General population	Oral	1.5 mg/kg bw/day

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]

Duration:	Route of exposure:	DNEL:
Long term – Local effects - General population	Inhalation	28 $\mu\text{g}/\text{m}^3$
Long term – Local effects - Workers	Inhalation	170 $\mu\text{g}/\text{m}^3$

PNEC

2-aminoethanol;ethanolamine

Route of exposure:	Duration of Exposure:	PNEC:
Freshwater		70 $\mu\text{g}/\text{L}$



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

Freshwater sediment	357 µg/kg
Intermittent release (freshwater)	28 µg/L
Marine water	7 µg/L
Marine water sediment	35.7 µg/kg
Sewage treatment plant	100 mg/L
Soil	1.29 mg/kg

8.2. Exposure controls

Compliance with the given occupational exposure limits values should be controlled on a regular basis.

General recommendations

Smoking, drinking and consumption of food is not allowed in the work area.

Exposure scenarios

There are no exposure scenarios implemented for this product.

Exposure limits

Professional users are subjected to the legally set maximum concentrations for occupational exposure. See occupational hygiene limit values above.

Appropriate technical measures

The formation of vapours must be kept at a minimum and below current limit values (see above). Installation of a local exhaust system if normal air flow in the work room is not sufficient is recommended. Ensure eyewash and emergency showers are clearly marked.

Apply standard precautions during use of the product. Avoid inhalation of vapours.

Hygiene measures

Wash hands after use.

Measures to avoid environmental exposure

No specific requirements.

Individual protection measures, such as personal protective equipment

Generally

Use only UKCA marked protective equipment.

Respiratory Equipment

Type	Class	Colour	Standards
Respiratory protection is not needed in the event of adequate ventilation.			

Skin protection

Recommended	Type/Category	Standards
Wear appropriate protection clothing, e.g. coveralls in polypropylene or working clothes in cotton or polyester.	-	-



Hand protection

Material	Glove thickness (mm)	Breakthrough time (min.)	Standards
No specific requirements	-	-	-

Eye protection

Type	Standards
No special when used as intended.	-



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state

Liquid

Colour

Various colours

Odour / Odour threshold

Mild

pH

8-9

Density (g/cm³)

1.3

Kinematic viscosity

15000 mPa.s (25 °C)

Particle characteristics

Not applicable

Phase changes

Melting point/Freezing point (°C)

No relevant or available data due to the nature of the product.

Softening point/range (°C)

Does not apply to liquids.

Boiling point (°C)

100

Vapour pressure

No relevant or available data due to the nature of the product.

Relative vapour density

No relevant or available data due to the nature of the product.

Decomposition temperature (°C)

Not applicable

Data on fire and explosion hazards

Flash point (°C)

No relevant or available data due to the nature of the product.

Flammability (°C)

No relevant or available data due to the nature of the product.

Auto-ignition temperature (°C)

No relevant or available data due to the nature of the product.

Lower and upper explosion limit (% v/v)

No relevant or available data due to the nature of the product.

Solubility

Solubility in water

Completely soluble

n-octanol/water coefficient (LogKow)

No relevant or available data due to the nature of the product.

Solubility in fat (g/L)

No relevant or available data due to the nature of the product.

9.2. Other information

Oxidizing properties

No relevant or available data due to the nature of the product.

Other physical and chemical parameters

No data available.



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

SECTION 10: Stability and reactivity

10.1. Reactivity

No data available.

10.2. Chemical stability

The product is stable under the conditions, noted in section 7 "Handling and storage".

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Frost

10.5. Incompatible materials

No specific requirements

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008 as retained and amended in UK law

Acute toxicity

Based on available data, the classification criteria are not met.

Skin corrosion/irritation

Based on available data, the classification criteria are not met.

Serious eye damage/irritation

Based on available data, the classification criteria are not met.

Respiratory sensitisation

Based on available data, the classification criteria are not met.

Skin sensitisation

Based on available data, the classification criteria are not met.

Germ cell mutagenicity

Based on available data, the classification criteria are not met.

Carcinogenicity

Based on available data, the classification criteria are not met.

Reproductive toxicity

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

11.2. Information on other hazards

Long term effects

None known.

Endocrine disrupting properties

This mixture/product does not contain any substances known to have hormone-disrupting properties in relation to health.

Other information

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$] has been classified by IARC as a group 2B carcinogen.



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

SECTION 12: Ecological information

12.1. Toxicity

No data available.

12.2. Persistence and degradability

Based on available data, the classification criteria are not met.

12.3. Bioaccumulative potential

Based on available data, the classification criteria are not met.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.

12.6. Endocrine disrupting properties

This mixture/product does not contain any substances considered to have endocrine-disrupting properties in relation to the environment.

12.7. Other adverse effects

None known.

SECTION 13: Disposal considerations

Waste treatment methods

Product is not covered by regulations on dangerous waste.

Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.

EWC code

Not applicable.

Specific labelling

Contaminated packing

Packaging containing residues of the product must be disposed of similarly to the product.

SECTION 14: Transport information

	14.1 UN / ID	14.2 UN proper shipping name	14.3 Hazard class(es)	14.4 PG*	14.5 Env**	Other information:
ADR	-	-	-	-	-	-
IMDG	-	-	-	-	-	-
IATA	-	-	-	-	-	-

* Packing group

** Environmental hazards

Additional information

Not dangerous goods according to ADR, IATA and IMDG.

14.6. Special precautions for user

Not applicable.

14.7. Maritime transport in bulk according to IMO instruments

No data available.

SECTION 15: Regulatory information



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Restrictions for application

No special.

Demands for specific education

No specific requirements.

Control of Major Accident Hazards (COMAH) - Categories / dangerous substances

Not applicable.

Additional information

Not applicable.

Sources

Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.

Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures (CLP) as retained and amended in UK law.

Regulation (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) as retained and amended in UK law.

15.2. Chemical safety assessment

No

SECTION 16: Other information

Full text of H-phrases as mentioned in section 3

H302, Harmful if swallowed.

H312, Harmful in contact with skin.

H314, Causes severe skin burns and eye damage.

H318, Causes serious eye damage.

H332, Harmful if inhaled.

H335, May cause respiratory irritation.

H412, Harmful to aquatic life with long lasting effects.

Abbreviations and acronyms

ADN = European Provisions concerning the International Carriage of Dangerous Goods by Inland Waterway

ADR = The European Agreement concerning the International Carriage of Dangerous Goods by Road

ATE = Acute Toxicity Estimate

BCF = Bioconcentration Factor

CAS = Chemical Abstracts Service

CE = Conformité Européenne (European conformity)

CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]

CSA = Chemical Safety Assessment

CSR = Chemical Safety Report

DMEL = Derived Minimal Effect Level

DNEL = Derived No Effect Level

EINECS = European Inventory of Existing Commercial chemical Substances

ES = Exposure Scenario

EUH statement = CLP-specific Hazard statement

EuPCS = European Product Categorisation System

EWC = European Waste Catalogue

GHS = Globally Harmonized System of Classification and Labelling of Chemicals

GWP = Global warming potential

IARC = International Agency for Research on Cancer (IARC)

IATA = International Air Transport Association

IBC = Intermediate Bulk Container

IMDG = International Maritime Dangerous Goods

LogPow = logarithm of the octanol/water partition coefficient

MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)

OECD = Organisation for Economic Co-operation and Development



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

PBT = Persistent, Bioaccumulative and Toxic

PNEC = Predicted No Effect Concentration

RID = The Regulations concerning the International Carriage of Dangerous Goods by Rail

RRN = REACH Registration Number

SCL = A specific concentration limit

SVHC = Substances of Very High Concern

STOT-RE = Specific Target Organ Toxicity - Repeated Exposure

STOT-SE = Specific Target Organ Toxicity - Single Exposure

TWA = Time weighted average

UN = United Nations

UVBC = Unknown or variable composition, complex reaction products or of biological materials

VOC = Volatile Organic Compound

vPvB = Very Persistent and Very Bioaccumulative

Additional information

Not applicable.

The safety data sheet is validated by

ST

Other

A change (in proportion to the last essential change (first cipher in SDS version, see section 1)) is marked with a triangle.

The information in this safety data sheet applies only to this specific product (mentioned in section 1) and is not necessarily correct for use with other chemicals/products.

It is recommended to hand over this safety data sheet to the actual user of the product. Information in this safety data sheet cannot be used as a product specification.

Country-language: GB-en