

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name

edding industry paint marker ink (black) contained in: edding 8750

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Ink for use in felt pens

Uses advised against

No data available.

1.3 Details of the supplier of the safety data sheet

Address

edding International GmbH

Bookkoppel 7

D-22926 Ahrensburg

Telephone no. +49 (0) 41 02 / 80 8-0

Information provided by / telephone

+49 (0)4102 - 808-0

Advice on Safety Data Sheet

sdb_info@umco.de

1.4 Emergency telephone number

For medical advice (in German and English):

+49 (0)30 30686 790 (Giftnotruf Berlin)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification in accordance with Regulation (EC) No 1272/2008 (CLP)

Flam. Liq. 3; H226

Skin Irrit. 2; H315

Classification information

This product is assessed and classified using the methods and criteria below referred to in Article 9 of Regulation (EC) n° 1272/2008:

Physical hazards: determined through assessment data based on the methods or standards referred to in part 2 of Annex I to CLP

Health hazards and environmental hazards: determined through toxicological and ecotoxicological assessment data based on the methods or standards referred to in Part 3, 4 and 5 of Annex I to CLP.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 (CLP Regulation)

Hazard pictograms



GHS02



GHS07

Signal word

Warning

Hazard statement(s)

H226

Flammable liquid and vapour.

H315

Causes skin irritation.

Precautionary statement(s)

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P370+P378	In case of fire: Use water spray, extinguishing powder, foam or CO2 to extinguish.
P501	Dispose of contents/container to a facility in accordance with local and national regulations.

Labelling information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

2.3 Other hazards

No data available.

SECTION 3: Composition/information on ingredients
3.1 Substances

Not applicable. The product is not a substance.

3.2 Mixtures
Chemical characterization

Mixture (preparation)

Hazardous ingredients

No	Substance name	Additional information	
	CAS / EC / Index / REACH no	Classification (EC) 1272/2008 (CLP)	Concentration
			%
1	xylene		
	1330-20-7 215-535-7 601-022-00-9 -	Acute Tox. 4*; H312 Acute Tox. 4*; H332 Flam. Liq. 3; H226 Skin Irrit. 2; H315	>= 50.00 - < 70.00 wt%
2	DESTILLATES (PETROLEUM), HYDRODESULFURIZED MIDDLE		pls. refer to footnote (1)
	64742-80-9 265-183-3 649-223-00-0 -	Asp. Tox. 1; H304 EUH066	< 5.00 wt%
3	ETHYLCYCLOHEXANE		
	1678-91-7 216-835-0 - -	Flam. Liq. 2; H225	< 2.50 wt%
4	CARBON BLACK		
	1333-86-4 215-609-9 - -	-	>= 10.00 - < 25.00 wt%

Full Text for all H-phrases and EUH-phrases: pls. see section 16

(*, **, ***, ****) Detailed explanation pls. refer to CLP regulation No. 1272/2008, annex VI, 1.2

(1) Aberrant from/in addition to the classification set out in Annex VI, this substance is classified according to European Regulation (EC) No 1272/2008 (CLP), Article 4 (3), paragraph 2.

No	Note	Specific concentration limits	M-factor (acute)	M-factor (chronic)
1	C	-	-	-
2	N	-	-	-

Full text for the notes: pls. see section 16 "Notes relating to the identification, classification and labelling of substances ((EC) No 1272/2008, Annex VI)".

Acute toxicity estimate (ATE) values

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

No	oral	dermal	inhalative
1		2000 mg/kg bodyweight	

3.3 Other information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

In case of persisting adverse effects, consult a physician. Remove contaminated clothing and shoes immediately, and launder thoroughly before reusing.

After inhalation

Remove affected person from the immediate area. Ensure supply of fresh air.

After skin contact

Wash off immediately with soap and water.

After eye contact

Separate eyelids, wash the eyes thoroughly with water (15 min.).

After ingestion

Rinse the mouth thoroughly with water. Call a doctor immediately. Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

No data available.

4.3 Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Foam; Extinguishing powder; Carbon dioxide

Unsuitable extinguishing media

No data available.

5.2 Special hazards arising from the substance or mixture

In the event of fire, the following can be released: Carbon dioxide (CO₂); Carbon monoxide (CO)

5.3 Advice for firefighters

Cool endangered containers with water spray jet. Use self-contained breathing apparatus. Wear protective clothing. Suppress gases/vapours/mists with water spray jet.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Refer to protective measures listed in sections 7 and 8. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Keep away from ignition sources.

For emergency responders

No data available. Personal protective equipment (PPE) - see Section 8.

6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater. Do not discharge into the subsoil/soil.

6.3 Methods and material for containment and cleaning up

Take up with absorbent material (e.g., sand, kieselguhr, universal binder). When collected, handle material as described under the section heading "Disposal considerations".

6.4 Reference to other sections

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

No data available.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling

Provide good ventilation at the work area (local exhaust ventilation, if necessary). Risks inherent to handling the product must be minimised by applying the appropriate protective and preventive measures. Working processes should - so far as possible, according to the state of the art - be designed to rule out bodily contact or the release of hazardous substances.

General protective and hygiene measures

Do not eat, drink or smoke during work time. Keep away from foodstuffs and beverages. Avoid contact with eyes and skin. Remove soiled or soaked clothing immediately. Do not inhale vapours. Provide eye wash fountain in work area. Have emergency shower available.

Advice on protection against fire and explosion

Vapours can form an explosive mixture with air. Take precautionary measures against static charges. Keep away from sources of heat and ignition. Use explosion-proof equipment/fittings and non-sparking tools.

7.2 Conditions for safe storage, including any incompatibilities

Technical measures and storage conditions

Keep container tightly closed in a cool, well-ventilated place. Protect from heat and direct sunlight.

Requirements for storage rooms and vessels

Containers which are opened must be carefully closed and kept upright to prevent leakage. Always keep in containers of same material as the original.

Incompatible products

None known

7.3 Specific end use(s)

No data available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values

No	Substance name	CAS no.	EC no.
1	xylene	1330-20-7	215-535-7
	2000/39/EC		
	Xylene, mixed isomers, pure		
	WEL short-term (15 min reference period)	442	mg/m ³ 100 ppm
	WEL long-term (8-hr TWA reference period)	221	mg/m ³ 50 ppm
	Skin resorption / sensibilisation	Skin	
	List of approved workplace exposure limits (WELs) / EH40		
	Xylene, o-, m-, p- or mixed isomers		
	WEL short-term (15 min reference period)	441	mg/m ³ 100 ppm
	WEL long-term (8-hr TWA reference period)	220	mg/m ³ 50 ppm
	Comments	Sk, BMGV	
2	CARBON BLACK	1333-86-4	215-609-9
	List of approved workplace exposure limits (WELs) / EH40		
	Carbon black		
	WEL short-term (15 min reference period)	7	mg/m ³
	WEL long-term (8-hr TWA reference period)	3.5	mg/m ³

8.2 Exposure controls

Appropriate engineering controls

No data available.

Personal protective equipment

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

Respiratory protection

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of aerosol and mist formation, take appropriate measures for breathing protection in the event workplace threshold values are not specified.

Eye / face protection

Safety glasses with side protection shield (EN 166)

Hand protection

Sufficient protection is given wearing suitable protective gloves checked according to i.e. EN 374, in the event of risk of skin contact with the product. Before use, the protective gloves should be tested in any case for its specific workstation suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Other

Normal chemical work clothing.

Environmental exposure controls

No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

State of aggregation	
liquid	
Form/Colour	
liquid	
black	
Odour	
aromatic	
pH value	
No data available	
Boiling point / boiling range	
Value	138 °C
Melting point/freezing point	
No data available	
Decomposition temperature	
No data available	
Flash point	
Value	23 °C
Ignition temperature	
Value	200 - 564 °C
Flammability	
No data available	
Lower explosion limit	
Value	1.00 % vol
Upper explosion limit	
Value	8.40 % vol
Vapour pressure	
Value	10 mm Hg
Reference temperature	28 °C
Relative vapour density	

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

No data available	
Relative density	
No data available	
Density	
Value	0.88 g/cm ³
Reference temperature	20 °C
Solubility in water	
Comments	insoluble
Solubility	
No data available	
Partition coefficient n-octanol/water (log value)	
No data available	
Viscosity	
Value	800 mPa*s
Type	dynamic
Particle characteristics	
No data available	

9.2 Other information

Other information
No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity

No data available.

10.2 Chemical stability

No data available.

10.3 Possibility of hazardous reactions

No data available.

10.4 Conditions to avoid

Heat

10.5 Incompatible materials

None known.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity			
No	Substance name	CAS no.	EC no.
1	xylene	1330-20-7	215-535-7
LD50		8700	mg/kg bodyweight
Species	rat		
Source	Manufacturer		
Acute dermal toxicity (result of the ATE calculation for the mixture)			
No	Product Name		
1	edding industry paint marker ink (black) contained in: edding 8750		
Comments	The result of the applied calculation method according to the		

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

	European Regulation (EC) 1272/2008 (CLP), Paragraph 3.1.3.6, Part 3 of Annex I is outside the values that imply a classification / labelling of this mixture according to table 3.1.1 defining the respective categories (ATE dermal > 2000 mg/kg).
--	---

Acute dermal toxicity			
No	Substance name	CAS no.	EC no.
1	xylene	1330-20-7	215-535-7
LD50		2000	mg/kg bodyweight
Species	rabbit		
Source	Manufacturer		

Acute inhalational toxicity (result of the ATE calculation for the mixture)	
No	Product Name
1	edding industry paint marker ink (black) contained in: edding 8750
Comments	The result of the applied calculation method according to the European Regulation (EC) 1272/2008 (CLP), Paragraph 3.1.3.6, Part 3 of Annex I is outside the values that imply a classification / labelling of this mixture according to table 3.1.1 defining the respective categories (ATE for inhalation: > 20.000 ppmV (gases), > 20 mg/l (vapours), > 5 mg/l (dusts/mists).

Acute inhalational toxicity			
No	Substance name	CAS no.	EC no.
1	xylene	1330-20-7	215-535-7
LC50		6350	mg/l
Duration of exposure		4	h
State of aggregation	Vapour		
Species	rat		
Source	Manufacturer		
Evaluation/classification	Based on available data, the classification criteria are met.		

Skin corrosion/irritation
No data available

Serious eye damage/irritation
No data available

Respiratory or skin sensitisation
No data available

Germ cell mutagenicity
No data available

Reproduction toxicity
No data available

Carcinogenicity
No data available

STOT - single exposure
No data available

STOT - repeated exposure
No data available

Aspiration hazard
No data available

Delayed and immediate effects as well as chronic effects from short and long-term exposure
Inhalation of vapours may lead to headache, drowsiness and dizziness. Repeated and prolonged skin contact may cause removal of natural fat from the skin and irritation of the skin. Eye contact with the product may lead to irritation.

11.2 Information on other hazards

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

Endocrine disrupting properties

No data available.

Other information

No data available.

SECTION 12: Ecological information

12.1 Toxicity

Toxicity to fish (acute)

No data available

Toxicity to fish (chronic)

No data available

Toxicity to Daphnia (acute)

No data available

Toxicity to Daphnia (chronic)

No data available

Toxicity to algae (acute)

No data available

Toxicity to algae (chronic)

No data available

Bacteria toxicity

No data available

12.2 Persistence and degradability

No data available.

12.3 Bioaccumulative potential

No data available.

12.4 Mobility in soil

No data available.

12.5 Results of PBT and vPvB assessment

No data available.

12.6 Endocrine disrupting properties

No data available.

12.7 Other adverse effects

No data available.

12.8 Other information

Other information

Ecological data are not available.

Do not discharge product unmonitored into the environment.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

Packaging

Residues must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

SECTION 14: Transport information

14.1 Transport ADR/RID/ADN

Class	3
Classification code	F1
Packing group	III
Hazard identification no.	30
UN number	UN1263
Proper shipping name	PAINT
Tunnel restriction code	D/E
Label	3
Comments	Containers with a capacity <= 450 ltrs are not subject to ADR-regulations (refer to 2.2.3.1.5.)

14.2 Transport IMDG

Class	3
Packing group	III
UN number	UN1263
Proper shipping name	PAINT
EmS	F-E, S-E
Label	3
Comments	Containers with a capacity <= 450 ltrs are not subjected to IMDG regulations, chapter 4.1, 5.2 and 6.1 (see IMDG-Code 2.3.2.5)

14.3 Transport ICAO-TI / IATA

Class	3
Packing group	III
UN number	UN1263
Proper shipping name	Paint
Label	3

14.4 Other information

No data available.

14.5 Environmental hazards

Information on environmental hazards, if relevant, please see 14.1 - 14.3.

14.6 Special precautions for user

No data available.

14.7 Maritime transport in bulk according to IMO instruments

Not relevant

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No 1907/2006 (REACH) Annex XIV (List of substances subject to authorisation)

According to the data available and/or specifications supplied by upstream suppliers, this product does not contain any substances considered as substances requiring authorisation as listed on Annex XIV of the REACH regulation (EC) 1907/2006.

REACH candidate list of substances of very high concern (SVHC) for authorisation

According to available data and the information provided by preliminary suppliers, the product does not contain substances that are considered substances meeting the criteria for inclusion in annex XIV (List of Substances Subject to Authorisation) as laid down in Article 57 and article 59 of REACH (EC) 1907/2006.

Regulation (EC) No 1907/2006 (REACH) Annex XVII: RESTRICTIONS ON THE MANUFACTURE, PLACING ON THE MARKET AND USE OF CERTAIN DANGEROUS SUBSTANCES, MIXTURES AND ARTICLES

The product is considered being subject to REACH regulation (EC) 1907/2006 annex XVII.	No 3, 40
--	----------

Trade name: edding industry paint marker ink (black) contained in: edding 8750

Current version : 2.2.0, issued: 14.10.2021

Replaced version: 2.1.0, issued: 27.08.2019

Region: GB

Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances

This product is subject to Part I of Annex I, risk category:	P5c
--	-----

15.2 Chemical safety assessment

No data available.

SECTION 16: Other information

Sources of key data used to compile the data sheet:

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.

Directives 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164.

National Threshold Limit Values of the corresponding countries as amended in each case.

Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.

The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding section.

Full text of the H- and EUH- phrases drawn up in sections 2 and 3 (provided not already drawn up in these sections)

EUH066	Repeated exposure may cause skin dryness or cracking.
H225	Highly flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H312	Harmful in contact with skin.
H332	Harmful if inhaled.

Notes relating to the identification, classification and labelling of substances and mixtures ((EC) No 1272/2008, Annex VI)

C	Some organic substances may be marketed either in a specific isomeric form or as a mixture of several isomers. In this case the supplier must state on the label whether the substance is a specific isomer or a mixture of isomers.
N	The harmonised classification as a carcinogen applies unless the full refining history is known and it can be shown that the substance from which it is produced is not a carcinogen, in which case a classification in accordance with Title II of this Regulation shall be performed also for that hazard class.

Creation of the safety data sheet

UMCO GmbH

Georg-Wilhelm-Str. 187, D-21107 Hamburg

Tel.: +49 40 / 555 546 300 Fax: +49 40 / 555 546 357 e-mail: umco@umco.de

This information is based on our present knowledge and experience.

The safety data sheet describes products with a view to safety requirements.

It does not however, constitute a guarantee for any specific product properties and shall not establish a legally valid contractual relationship.

Alterations/supplements:

Alterations to the previous edition are marked in the left-hand margin.

Document protected by copyright. Alterations or reproductions require the express written permission of UMCO GmbH.

Prod-ID 25825