

LOGO! DM16 24, EXP. MODULE PU/I/O: 24V DC/24V DC/TRANS.,
8 DI/8 DO, 4TE FOR LOGO! 8



Installation type/mounting

Mounting	on 35 mm DIN rail, 4 spacing units wide
----------	---

Supply voltage

Rated value (DC)	Yes
• 24 V DC	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

Digital inputs

Number of digital inputs	8
Input voltage	
• Type of input voltage	DC
• for signal "0"	< 5 V DC
• for signal "1"	> 12 V DC

Input current

• for signal "0", max. (permissible quiescent current)	0.85 mA
• for signal "1", typ.	3.5 mA

Input delay (for rated value of input voltage)

for standard inputs	
— at "0" to "1", max.	1.5 ms
— at "1" to "0", max.	1.5 ms
Digital outputs	
Number of digital outputs	8
Short-circuit protection	Yes
Controlling a digital input	Yes
Output current	
• for signal "1" rated value	0.3 A
Parallel switching of two outputs	
• for uprating	No
Switching frequency	
• with resistive load, max.	10 Hz
• with inductive load, max.	0.5 Hz
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Dimensions	
Width	71.5 mm
Height	90 mm
Depth	58 mm
last modified:	24.02.2016