


Unit = mm



Roll ball type tilt switch

Voltage:	<12V
Current:	<20mA
Conductive time:	About 2ms
Closed resistance:	<10 ohm
Open resistance:	>10M ohm
Temperature range:	-40 to 80 °C
Pull force of terminal:	500gf for 1 minute
Humidity:	95% RH, 40 °C for 96 hours
Operating lifespan:	above 200000 circle

Features:

When the product tilt to Conductive terminal (A) more than 15°, is open circuit OFF-state, when trigger end (gold-plated pin end C) below the horizontal gradient greater than 15° angle, is closed circuit ON-state.

