



!!! product phase-out !!! the preferred successor is 3UG5642-1CW30 digital monitoring relay voltage monitoring, 22.5 mm from 10 to 600 V AC/DC overshoot and undershoot supply voltage: 24 V AC/DC 50 to 60 Hz DC and AC without electrical separation from the measuring circuit noise pulses delay 0.1 to 20 s hysteresis 0.1 to 300 V 1 changeover contact with or without fault buffer screw terminal

| | |
|--|---|
| product brand name | SIRIUS |
| product designation | Voltage monitoring relay with digital setting |
| product type designation | 3UG4 |
| General technical data | |
| product function | Voltage monitoring relay |
| design of the display | LCD |
| consumed active power | 2 W |
| insulation voltage for overvoltage category III according to IEC 60664 | |
| • with degree of pollution 3 rated value | 690 V |
| type of voltage | |
| • for monitoring | AC/DC |
| • of the control supply voltage | AC/DC |
| surge voltage resistance rated value | 4 kV |
| maximum permissible voltage for protective separation | |
| • between auxiliary and auxiliary circuit | 300 V |
| • between control and auxiliary circuit | 300 V |
| shock resistance according to IEC 60068-2-27 | sinusoidal half-wave 15 g / 11 ms |
| vibration resistance according to IEC 60068-2-6 | 1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2 g |
| mechanical service life (operating cycles) typical | 10 000 000 |
| electrical endurance (operating cycles) at AC-15 at 230 V typical | 100 000 |
| thermal current of the switching element with contacts maximum | 5 A |
| reference code according to IEC 81346-2 | K |
| relative repeat accuracy | 1 % |
| Substance Prohibitance (Date) | 05/01/2012 |
| SVHC substance name | Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1 |
| Net Weight | 0.137 kg |
| Product Function | |
| product function | |
| • undervoltage detection | Yes |
| • overvoltage detection | Yes |
| • voltage monitoring | Yes |
| • current monitoring | No |
| • overvoltage detection 1 phase | Yes |
| • overvoltage detection 3 phase | No |

| | |
|---|---------------|
| • overvoltage detection DC | Yes |
| • undervoltage detection 1 phase | Yes |
| • undervoltage detection 3 phases | No |
| • undervoltage detection DC | Yes |
| • voltage window recognition 1 phase | Yes |
| • voltage window recognition 3 phase | No |
| • voltage window recognition DC | Yes |
| • adjustable open/closed-circuit current principle | Yes |
| • external reset | Yes |
| • auto-RESET | Yes |
| measurable line frequency initial value | 40 Hz |
| measurable line frequency full-scale value | 500 Hz |
| Control circuit/ Control | |
| control supply voltage at AC | |
| • at 50 Hz rated value | 24 V |
| • at 50 Hz rated value | 24 ... 240 V |
| • at 60 Hz rated value | 24 V |
| • at 60 Hz rated value | 24 ... 240 V |
| control supply voltage at DC rated value | 24 V |
| control supply voltage at DC rated value | 24 ... 240 V |
| operating range factor control supply voltage rated value at DC | |
| • initial value | 0.85 |
| • full-scale value | 1.15 |
| operating range factor control supply voltage rated value at AC at 50 Hz | |
| • initial value | 0.85 |
| • full-scale value | 1.15 |
| operating range factor control supply voltage rated value at AC at 60 Hz | |
| • initial value | 0.85 |
| • full-scale value | 1.15 |
| starting time after the control supply voltage has been applied | 1 000 ms |
| Measuring circuit | |
| measurable line frequency | 40 ... 500 Hz |
| measurable voltage at AC | 10 ... 600 V |
| measurable voltage at DC | 10 ... 600 V |
| adjustable response delay time | |
| • when starting | 20 s |
| • with lower or upper limit violation | 0.1 ... 20 s |
| response time maximum | 450 ms |
| accuracy of digital display | +/-1 digit |
| relative temperature-related measurement deviation | 0.1 % |
| Precision | |
| relative metering precision | 5 % |
| Auxiliary circuit | |
| number of NC contacts delayed switching | 0 |
| number of NO contacts delayed switching | 0 |
| number of CO contacts delayed switching | 1 |
| operating frequency with 3RT2 contactor maximum | 5 000 1/h |
| Main circuit | |
| number of poles for main current circuit | 1 |
| operating voltage | |
| • at AC at 60 Hz rated value | 240 V |
| • at DC rated value | 24 V |
| ampacity of the output relay at AC-15 at 400 V at 50/60 Hz | 3 A |
| ampacity of the output relay at DC-13 | |
| • at 24 V | 1 A |
| • at 125 V | 0.2 A |

| | |
|---|--|
| • at 250 V | 0.1 A |
| operational current at 17 V minimum | 5 mA |
| continuous current of the DIAZED fuse link of the output relay | 4 A |
| Electromagnetic compatibility | |
| conducted interference | |
| • due to burst according to IEC 61000-4-4 | 2 kV |
| • due to conductor-earth surge according to IEC 61000-4-5 | 2 kV |
| • due to conductor-conductor surge according to IEC 61000-4-5 | 1 kV |
| field-based interference according to IEC 61000-4-3 | 10 V/m |
| electrostatic discharge according to IEC 61000-4-2 | 6 kV contact discharge / 8 kV air discharge |
| Galvanic isolation | |
| design of the electrical isolation | Protective separation |
| galvanic isolation | |
| • between input and output | Yes |
| • between the outputs | Yes |
| • between the voltage supply and other circuits | No |
| Electrical Safety | |
| protection class IP on the front according to IEC 60529 | IP20 |
| Connections/ Terminals | |
| product component removable terminal for auxiliary and control circuit | Yes |
| type of electrical connection | screw terminal |
| type of connectable conductor cross-sections | |
| • solid | 1x (0.5 ... 4 mm ²), 2x (0.5 ... 2.5 mm ²) |
| • finely stranded with core end processing | 1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²) |
| • for AWG cables solid | 2x (20 ... 14) |
| • for AWG cables stranded | 2x (20 ... 14) |
| connectable conductor cross-section | |
| • solid | 0.5 ... 4 mm ² |
| • finely stranded with core end processing | 0.5 ... 2.5 mm ² |
| AWG number as coded connectable conductor cross section | |
| • solid | 20 ... 14 |
| • stranded | 20 ... 14 |
| tightening torque with screw-type terminals | 1.2 ... 0.8 N·m |
| Installation/ mounting/ dimensions | |
| mounting position | any |
| fastening method | snap-on mounting |
| height | 92 mm |
| width | 22.5 mm |
| depth | 91 mm |
| required spacing | |
| • with side-by-side mounting | |
| — forwards | 0 mm |
| — backwards | 0 mm |
| — upwards | 0 mm |
| — downwards | 0 mm |
| — at the side | 0 mm |
| • for grounded parts | |
| — forwards | 0 mm |
| — backwards | 0 mm |
| — upwards | 0 mm |
| — at the side | 0 mm |
| — downwards | 0 mm |
| • for live parts | |
| — forwards | 0 mm |
| — backwards | 0 mm |
| — upwards | 0 mm |

— at the side

0 mm

Ambient conditions

| | |
|---|----------------|
| installation altitude at height above sea level maximum | 2 000 m |
| ambient temperature | |
| • during operation | -25 ... +60 °C |
| • during storage | -40 ... +85 °C |
| • during transport | -40 ... +85 °C |

Approvals Certificates

| | |
|--|-----------|
| Environmental Product Declaration | |
| • global warming potential [CO2 eq] / during manufacturing | 4.44 kg |
| • global warming potential [CO2 eq] / during sales | 0.0341 kg |
| • global warming potential [CO2 eq] / during operation | 13.7 kg |
| • global warming potential [CO2 eq] / after end of life | -1.06 kg |
| • global warming potential [CO2 eq] / total | 17.1 kg |

| | |
|--------------------|---------------------------------|
| Environment | General Product Approval |
|--------------------|---------------------------------|

[Environmental Conformations](#)



| | | | |
|---------------------------------|------------|--------------------------|-----------------------------|
| General Product Approval | EMV | Test Certificates | Maritime application |
|---------------------------------|------------|--------------------------|-----------------------------|



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



| | | |
|-----------------------------|--------------|----------------|
| Maritime application | other | Railway |
|-----------------------------|--------------|----------------|



[Confirmation](#)

[Confirmation](#)

[Special Test Certificate](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UG4632-1AA30>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UG4632-1AA30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UG4632-1AA30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UG4632-1AA30&lang=en

last modified:

4/4/2026