

## EVH2S7P0CK

EVlink Wallbox - 7.4 kW - attached cable T2 - charging station



### Main

Range	EVlink
Product name	EVlink Wallbox
Product or component type	Charging station
Device short name	EVH2
Poles description	1P + N
Mounting mode	Wall-mounted
Offer type	Standard
Nominal output power	7.4 kW 32 A
Socket number	1
Output type	Attached cable T2 4 m
Access control system	Key

### Complementary

[Us] rated supply voltage	220...240 V AC 50/60 Hz
Earthing system	TN TT
Number of inputs	1
Input type	Contact for power limitation Contact for delayed charging
Control type	1 white button, function: stop/restart Green button, function: cable unlocking
Local signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	330 mm
Depth	170 mm
Product weight	7.5 kg
Colour	White RAL 9003 Grey RAL 7016
Standards	IEC 61851-1 IEC 61851-22 IEC 62196-1 IEC 62196-2
Product certifications	CE CB

### Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
ambient air temperature for operation	-30...50 °C
ambient air temperature for storage	-40...80 °C
relative humidity	5...95 %

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1514 - Schneider Electric declaration of conformity

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.