

ZCKY59

limit switch lever ZCKY - th.plastic round rod
lever 6 mm L=200 mm - -40..70°C



ZCKY 59

Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ XCKL XCKM XCKS
Associated head	ZCKD05 ZCKE05
Movement of operating head	Rotary
Type of operator	Rod lever spring return thermoplastic (round rod 6 mm, L = 200 mm)
Type of approach	Lateral approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature
Ambient air temperature for storage	-40...70 °C for standard environment -40...70 °C for low temperature
Environmental characteristic	Low temperature Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1005 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations