



Main

Range	EVlink
Product name	EVlink Wallbox
Product or component type	Charging station
Device short name	EVH2
Poles description	3P + N
Mounting mode	Wall-mounted
Offer type	Standard
Nominal output power	11 kW 16 A
Socket outlet type	T2S
Socket number	1
Output type	Socket-outlet T2 with shutter
Access control system	Key

Complementary

[Us] rated supply voltage	380...415 V AC 50/60 Hz
Earthing system	TN TT
Number of inputs	1
Input type	Contact for power limitation Contact for delayed charging
Control type	1 white button, function: stop/restart Green button, function: cable unlocking
Local signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	331.5 mm
Depth	170 mm
Product weight	5.6 kg
Colour	Grey RAL 7016

White RAL 9003

Standards	IEC 62196-2 IEC 62196-1 IEC 61851-1 IEC 61851-22
Product certifications	CB CE

Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1514 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available