



## Main

|                           |                  |
|---------------------------|------------------|
| Product name              | SpaceLYnk        |
| Product or component type | Logic controller |

## Complementary

|                             |   |
|-----------------------------|---|
| Communication port protocol | BACnet<br>Modbus<br>IP (Internet Protocol)<br>KNX   |
| [Us] rated supply voltage   | 24 V DC   |
| Power consumption in W      | 2 W   |
| LED indicator               | Green LED (CPU load)<br>Green/Red LED (KNX powered/reset)   |
| Physical interface          | 1 x RJ45<br>1 x RS485<br>1 x RS232<br>1 x TP-UART2  |
| Port Ethernet               | 10BASE-T/100BASE-TX   |
| Integrated connection type  | 1 x USB 2.0 port  |
| Control type                | RESET push-button   |
| Connections - terminals     | KNX bus : bus terminal, 2 x 0.8 mm <sup>2</sup><br>Power supply : clamp terminal, 1.5 mm <sup>2</sup><br>Serial : clamp terminal, 1.5 mm <sup>2</sup> |
| Mounting support            | DIN rail  |
| Height                      | 90 mm   |
| Width                       | 52 mm   |
| Depth                       | 58 mm   |

## Environment

|                                       |            |
|---------------------------------------|------------|
| Ambient air temperature for operation | -5...45 °C |
| Operating altitude                    | <= 2000 m  |
| Relative humidity                     | 0...93 %   |

|                         |                             |
|-------------------------|-----------------------------|
| IP degree of protection | IP20                        |
| Directives              | 2002/96/EC - WEEE directive |
| Standards               | IEC 60950-1                 |

## Offer Sustainability

|                               |   |
|-------------------------------|---|
| Sustainable offer status      | Green Premium product   |
| RoHS (date code: YYWW)        | Compliant - since 1426 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                         | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile | Available   |