



Main

Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	Easypact CVS PowerPact Multistandard Compact NSX
Voltage release type	Undervoltage release
[Uc] control circuit voltage	220...240 V AC 208...277 V AC

Complementary

Threshold tripping voltage	0.35...0.7 x Un - during opening time 0.85 x Un - during closing time
Supply holding power	5 VA
Supply inrush power	10 VA
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	Screw terminal 0...1.5 mm ²

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0835 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
