

# EVP2PE704

## EVlink Parking Spare Part Enclosure Grey 7kW 1xT2 with shutter



### Main

Range	EVlink
Product name	EVlink parking
Product or component type	Enclosure
Device short name	EVP2
Range compatibility	EVlink parking EVF2 charging station EVlink parking EVW2 charging station
Poles description	1P + Nfor control circuit 1P + Nfor power circuit
Mounting mode	Wall-mounted Floor-standing
Offer type	Standard
Rated supply voltage	230 V AC 50/60 Hz power circuit 220...240 V AC 50/60 Hz control circuit
Earthing system	TN TT IT
Socket-outlet number	1
Socket-outlet type	Right side: T2 with shutter / silver plated contacts
Maximum supply current	32 Afor T2 with shutter
Max power	7 kWfor T2 with shutter

### Complementary

Control type	1 red push-button, function: stop 1 green illuminated push-button, function: start/unlock flap
Local signalling	On charge: 1 LED (green) (flashing) on side Available: 1 LED (green) on front Reserved: 1 LED (orange) on front Not operational: 1 LED (red) on front
Web server	Embedded
Ethernet service	Configuration via web server
Height	625 mm
Width	400 mm
Depth	206 mm
Net weight	20 kg

Colour	Grey (RAL 7016)
--------	-----------------

## Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK10 socket-outlet conforming to IEC 61851-22
Ambient air temperature for operation	-25...50 °C conforming to IEC 61851-22
Ambient air temperature for storage	-40...80 °C
Operating altitude	0...2000 m conforming to IEC 61851-22
Relative humidity	0...95 %

## Contractual warranty

Warranty	18 months
----------	-----------