

Product information

97 55 14

Self-Adjusting Crimping Pliers for wire ferrules

With lateral access




- Narrow handle width and improved ergonomics
- Expanded capacity of hexagonal crimping up to 10 mm²
- Hexagonal compression for confined connection dimensions
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm² or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 55 14
EAN	4003773084860
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips
weight	445 g
Dimensions	180 x 75 x 21 mm
Reach	yes
RohS	no

Technical details



Applications	Wire ferrules
Capacity in square millimetres	0.08 — 10 mm ²
Number of crimping positions	1
AWG	28 — 8

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003

technical change and errors excepted

