

Product Code: WA227

Description: 100A 1 Pole 5 x 35mm<sup>2</sup> Link Box



### General Information

<b>Dimensions</b>	66mm (W) x 49mm (D) x 34mm (H)
<b>Finish</b>	Black
<b>Materials</b>	Body: Urea Terminal Screws: Steel and Yellow Passivated Earth Terminals: Brass
<b>Maximum Voltage</b>	250V~ 50Hz
<b>Load Rating</b>	100A
<b>Terminal Size</b>	8.7mmø
<b>Terminal Torque</b>	2.5Nm
<b>Terminal Capacity</b>	1 x 35mm <sup>2</sup>
<b>Entry Dimensions</b>	9.7mmø
<b>Ingress Protection</b>	IP20
<b>Termination Type</b>	Screw
<b>Operational Temperature</b>	-20°C to +55°C
<b>Warranty</b>	10 Years
<b>Standards</b>	BS 5733: 2010

### Additional Information

Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.  
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.  
Tamper Proof Sealable