


Low-Profile Slide Series

Application

- ✓ Audio, Home appliance, Lighting control, etc.

Feature

- ✓ Smooth slide feeling.



■Specification

Operating Temperature Range	-10 °C~70°C
Standard Resistance Tolerance	±20%
Insulation Resistance	100 MΩ Min. at 250V DC
Dielectric Strength	1 minute at 300V AC
Travel Distance	15mm, 30mm, 45mm, 60mm
Operating Force	30~250 gf.cm
Sliding Life	15,000 cycles

■How to order

RA1521F-20 – 15C1 - B10K – 01

Model

Lever Type

Taper and Resistance Value

Ex:

Order Code	Taper	Resistance Value
A100K	Audio/Log/A	100KΩ
B10K	Linear/B	10KΩ

Taper: A and B

Resistance Value: 1KΩ to 500KΩ and 1MΩ

*Contact us for other requirements.

Click and Dust cover

Order Code	Description
01	With dust cover
Blank	Without center click and dust cover

Low-Profile Slide Series

■ Model Description

Model	Number of Unit	Travel Distance	Type of Terminal	Tap	Mounting Height
RA1521F-20	Single Unit	15mm	PC board (vertical)	N/A	6.5mm
RA3021F-20	Single Unit	30mm	PC board (vertical)	N/A	6.5mm
RA4521F-20	Single Unit	45mm	PC board (vertical)	N/A	6.5mm
RA6021F-20	Single Unit	60mm	PC board (vertical)	N/A	6.5mm
RA3022F-20	Dual Unit	30mm	PC board (vertical)	N/A	6.5mm
RA4522F-20	Dual Unit	45mm	PC board (vertical)	N/A	6.5mm
RA6022F-20	Dual Unit	60mm	PC board (vertical)	N/A	6.5mm
RA1521F-202	Single Unit	15mm	PC board (vertical)	N/A	6.5mm
RA3021F-202	Single Unit	30mm	PC board (vertical)	N/A	6.5mm
RA4521F-202	Single Unit	45mm	PC board (vertical)	N/A	6.5mm
RA6021F-202	Single Unit	60mm	PC board (vertical)	N/A	6.5mm
RA3021F-203	Single Unit	30mm	PC board (vertical)	N/A	8mm
RA4521F-203	Single Unit	45mm	PC board (vertical)	N/A	8mm
RA1522F-202	Dual Unit	15mm	PC board (vertical)	N/A	6.5mm
RA3022F-202	Dual Unit	30mm	PC board (vertical)	N/A	6.5mm
RA4522F-202	Dual Unit	45mm	PC board (vertical)	N/A	6.5mm
RA6022F-202	Dual Unit	60mm	PC board (vertical)	N/A	6.5mm
RA4522F-203	Dual Unit	45mm	PC board (vertical)	N/A	8mm

[Back to top](#)




Low-Profile Slide Series

Order Code	Outline Drawing
RA□□21F-20	

[Back to top](#)

Low-Profile Slide Series

■ Lever Type

Model	RA□□21F and RA□□22F							
Lever Type	C1				VA	DA		
Dimension	Metal lever t=1.2 				Insulated lever 	Insulated lever 		
Length(L)	F	3	7	10	10.5	10	15	20
	L	8	10	15				

Design and specifications presented here are for the standard parts only. Please kindly contact us for your special requests and ask for the current technical specifications before purchase and/or use.

[Back to top](#)