

Data Sheet

Inductive proximity sensor M12, 4mm, line



Technical data

Operating voltage: 13 - 36V DC (best input 24V)

Outputs: PNP

Size: M12

Material: Brass

IP rating: IP67

Cable length: 2m

Switching distance (max.): 4mm

Length: 41.7mm

Switching frequency: 1800Hz

Operation temperature: -30°C ~ +80°C

Storage temperature: -30°C ~ +80°C

Insulation resistance: $\geq 50\text{M}\Omega$ Min (500VDC)

Dielectric strength: 1500VAC 50/60Hz

Vibration resistance: 10-55Hz/Min, Amplitude: 1mm

Shock resistance: 500M/S² (50G)

Item no.: 2348265

Data Sheet



Wiring diagram

