

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3
Revision Date 06.11.2023

Print Date 06.11.2023
Specification Number: 350000043409

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

- 1.1 Product identifier** : Janitol Original
- UFI** : GGY3-00A9-1001-2MW2
- 1.2 Relevant identified uses of the substance or mixture and uses advised against**
- Use of the Substance/Mixture** : Washing and cleaning products (including solvent based products)
- Uses advised against** : None identified
- 1.3 Details of the supplier of the safety data sheet** : SC Johnson Professional
Denby Hall Way,
Denby,
DE58JZ, UK
- Telephone** : +44 (0) 1773 855100 / +49 (0) 2151 73801827
- E-mail address** : talktous@scj.com
- 1.4 Emergency telephone number** : National Poisons Information Centre (Eire) 01-8092566/8379964

SECTION 2: HAZARDS IDENTIFICATION**2.1 Classification of the substance or mixture**

Classification according to Regulation (EC) No 1272/2008 (CLP)

Hazard classification	Hazard category	Hazards identification
Skin irritation	Category 2	Causes skin irritation.
Serious eye damage	Category 1	Causes serious eye damage.

2.2 Label elements

Labelling according to Regulation (EC) No. 1272/2008 (CLP)

Hazard symbols

Signal word
Danger

Contains
tetrasodium ethylene diamine tetraacetate

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

caustic soda

Hazard statements

(H315) Causes skin irritation.

(H318) Causes serious eye damage.

Precautionary statements

(P302 + P352) IF ON SKIN: Wash with plenty of soap and water.

(P305 + P351 + P338) IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

(P314) Get medical advice/ attention if you feel unwell.

(P501) Dispose of contents /container in accordance with local regulations.

(P280) Wear protective gloves / eye protection.

EUH Statements

(EUH210) Safety data sheet available on request.

Detergents regulations: **Contains**

< = 5% EDTA and salts, amphoteric surfactants,

2.3 Other hazards: **Endocrine Disruptor**

The mixture does not contain any substances >0.1% that are included in the list established in accordance with Article 59(1) for having endocrine disrupting properties

PBT and vPvB substance

The mixture does not contain any substances >0.1% that meet the criteria for persistent, bioaccumulative and toxic or very persistent and very bioaccumulative in accordance with Annex XIII.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**3.1 Mixtures****Hazardous components:**

Chemical name	CAS-No./EC-No.	Reg. No.	Classification according to Regulation (EC) No 1272/2008 (CLP)	Weight percent	Specific Concentration limits, M-Factors, Acute Toxicity Estimates (ATE)
tetrasodium ethylene diamine tetraacetate	64-02-8 / 200-573-9	01-2119486762-27	Acute toxicity Category 4 H302 Serious eye damage Category 1 H318	>= 1.00 - < 5.00	ATE: Oral = 1,658 mg/kg Species: Rat

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

Chemical name	CAS-No./EC-No.	Reg. No.	Classification according to Regulation (EC) No 1272/2008 (CLP)	Weight percent	Specific Concentration limits, M-Factors, Acute Toxicity Estimates (ATE)
caustic soda	1310-73-2 / 215-185-5	01-2119982981-22	Skin corrosion Category 1A H314 Serious eye damage Category 1 H318	>= 1.00 - < 5.00	ATE: Oral = 325 mg/kg Species: Rat Dermal = 1,350 mg/kg Species: Rabbit SCL: Skin corrosion H314 >= 5 % Skin corrosion H314 2 - < 5 % Skin irritation H315 0.5 - < 2 % Eye irritation H319 0.5 - < 2 %
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	1471314-81-4 / 939-581-9		Short-term (acute) aquatic hazard Category 1 H400 Long-term (chronic) aquatic hazard Category 3 H412	>= 1.00 - < 5.00	M-Factor Acute = 1 ATE:
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	68424-85-1 / 270-325-2	01-2119983287-23	Skin corrosion Category 1B H314 Serious eye damage Category 1	>= 0.10 - < 0.50	M-Factor Acute = 10 M-Factor Chronic = 1 ATE: Oral = 426 mg/kg Species: Rat Dermal = 930 mg/kg

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

Chemical name	CAS-No./EC-No.	Reg. No.	Classification according to Regulation (EC) No 1272/2008 (CLP)	Weight percent	Specific Concentration limits, M-Factors, Acute Toxicity Estimates (ATE)
			H318 Long-term (chronic) aquatic hazard Category 1 H410 Short-term (acute) aquatic hazard Category 1 H400 Acute toxicity Category 4 H302 Acute toxicity Category 3 H311 Acute toxicity Category 3 H331		Species: Rat Inhalation = 0.054 mg/l Species: Rat

Additional Information

For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4: FIRST AID MEASURES**4.1 Description of first aid measures**

- Inhalation : Move to fresh air.
- Skin contact : Take off all contaminated clothing immediately.
Wash off with soap and plenty of water.
- Eye contact : Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
- Ingestion : If swallowed, do not induce vomiting: seek medical advice immediately and

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3
Revision Date 06.11.2023

Print Date 06.11.2023
Specification Number: 350000043409

show this container or label.

4.2 Most important symptoms and effects, both acute and delayed

Eyes	:	Causes serious eye damage.
Skin effect	:	Causes skin irritation.
Inhalation	:	May cause respiratory tract irritation.
Ingestion	:	May cause irritation to mouth, throat and stomach.

4.3 Indication of any immediate medical attention and special treatment needed

See Description of first aid measures unless otherwise stated.

SECTION 5: FIREFIGHTING MEASURES**5.1 Extinguishing media**

Suitable	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Unsuitable	:	None identified

5.2 Special hazards arising from the substance or mixture : In case of fire and/or explosion do not breathe fumes.

5.3 Advice for firefighters : In the event of fire, wear self-contained breathing apparatus. Wear suitable protective clothing and gloves.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.

6.2 Environmental precautions : Outside of normal use, avoid release to the environment. Prevent large amounts of product from entering drains. Do not flush into surface water or sanitary sewer system.

6.3 Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Clean residue from spill site.

6.4 Reference to other sections : For personal protection see section 8.

SAFETY DATA SHEET*(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)***Janitol Original**

Version 1.3
Revision Date 06.11.2023

Print Date 06.11.2023
Specification Number: 350000043409

For disposal considerations see section 13.

SECTION 7: HANDLING AND STORAGE

- 7.1 Precautions for safe handling** : For personal protection see section 8.
Avoid contact with skin and eyes.
Normal measures for preventive fire protection.
- 7.2 Conditions for safe storage, including any incompatibilities** : Do not freeze.
Keep out of the reach of children.
No decomposition if stored and applied as directed.
- 7.3 Specific end use(s)** : Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
Washing and cleaning products (including solvent based products)

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**8.1 Control parameters****Occupational Exposure Limit Values**

Components	CAS-No.	mg/m ³	ppm	Form of exposure	List
caustic soda	1310-73-2	2 mg/m ³			IE_STELS

Refer to current EN or National standard as appropriate.

8.2 Exposure controls

- Respiratory protection : In the case of vapour formation use a respirator with an approved filter.
- Hand protection : Wear suitable gloves.
Nitrile gloves – Thickness 0.12mm; Breakthrough time >2 hours.
- Eye/face protection : Safety glasses
- Skin and body protection : Wash contaminated clothing before re-use.
- Other information : Wash hands before breaks and at the end of workday.
- Environmental Exposure Controls : Refer to section 6.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**9.1 Information on basic physical and chemical properties**

- Physical State : liquid
- Colour : red

SAFETY DATA SHEET*(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)***Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

Odour	: characteristic
pH	: 12.5
Melting point/freezing point	: -20°C - 0°C
Initial boiling point and boiling range	: > 100 °C
Flash point	: > 93.4 °C
Flammability (solid, gas)	: not auto-flammable
Lower flammability or explosive limits	: Not measured as flashpoint >100 °C
Upper flammability or explosive limits	: Not measured as flashpoint >100 °C
Vapour pressure	: Not measured as flashpoint >100 °C
Vapour density	: Not measured as flashpoint >100 °C
Relative density	: 1.031 g/cm ³ at 20 °C
Solubility(ies)	: soluble
Partition coefficient: n-octanol/water	: Not required as the product is a mixture.
Auto-ignition temperature	: not auto-flammable
Decomposition temperature	: The substance or mixture is not classified self-reactive.
Viscosity, kinematic	: Test not applicable for this product type
Particle Characteristics	: Not required as mixture is a liquid

9.2 Other information

Other information	: Test not applicable for this product type
-------------------	---

SECTION 10: STABILITY AND REACTIVITY

10.1 Reactivity	: No dangerous reaction known under conditions of normal use.
------------------------	---

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

- 10.2 Chemical stability** : Stable under recommended storage conditions.
- 10.3 Possibility of hazardous reactions** : None known.
- 10.4 Conditions to avoid** : Extremes of temperature and direct sunlight.
- 10.5 Incompatible materials** : Do not mix with acids or any other household products. May release dangerous gases (chlorine).
- 10.6 Hazardous decomposition products** : No decomposition if stored and applied as directed.

SECTION 11: TOXICOLOGICAL INFORMATION**11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008****Acute oral toxicity**

Name	Method	Species	Dose
Product	LD50 Calculated		> 2,000 mg/kg

Acute inhalation toxicity

Name	Method	Species	Dose	Exposure time
Product	LC50 (dust and mist) Calculated		> 5 mg/l	

Acute dermal toxicity

Name	Method	Species	Dose
Product	LD50 Calculated		> 2,000 mg/kg

- Skin corrosion/irritation** : Causes skin irritation.EpiSkin
- Serious eye damage/eye irritation** : Causes serious eye damage.
- Skin sensitisation** : Based on available data, the classification criteria are not met.
- Germ cell mutagenicity** : Based on available data, the classification criteria are not met.

SAFETY DATA SHEET*(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)***Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

- Carcinogenicity : Based on available data, the classification criteria are not met.
- Toxicity for reproduction : Based on available data, the classification criteria are not met.
- STOT - single exposure : Based on available data, the classification criteria are not met.
- STOT - repeated exposure : Based on available data, the classification criteria are not met.
- Aspiration hazard : Based on available data, the classification criteria are not met.

11.2 Information on other hazards

- Endocrine Disrupting Properties : The mixture does not contain any substances >0.1% that are included in the list established in accordance with Article 59(1) for having endocrine disrupting properties
- Other information : None identified

SECTION 12: ECOLOGICAL INFORMATION**Product :** The product itself has not been tested.**12.1 Toxicity****Toxicity to fish**

Components	End point	Species	Value	Exposure time
tetrasodium ethylene diamine tetraacetate	LC50 static test	Lepomis macrochirus	41 mg/l	96 h
	NOEC	Danio rerio (zebra fish)	> 25.7 mg/l	35 d
caustic soda	LC50	Fish	35 - 189 mg/l	96 h
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	LC50 semi-static test estimated OECD Test Guideline 203	Oncorhynchus mykiss (rainbow trout)	1.8 mg/l	96 h
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	LC50 Measured OECD Test Guideline 203	Pimephales promelas (fathead minnow)	0.28 mg/l	96 h

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

	NOEC	Pimephales promelas (fathead minnow)	0.032 mg/l	34 d
--	------	---	------------	------

Toxicity to aquatic invertebrates

Components	End point	Species	Value	Exposure time
tetrasodium ethylene diamine tetraacetate	EC50	Daphnia magna (Water flea)	140 mg/l	48 h
	NOEC	Daphnia magna	25 mg/l	21 d
caustic soda	EC50	Daphnia magna (Water flea)	40.4 mg/l	48 h
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	EC50 static test estimated	Daphnia magna (Water flea)	0.96 mg/l	48 h
	NOEC semi-static test Measured	Daphnia magna	0.82 mg/l	21 d
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	EC50	Daphnia (water flea)	0.012 mg/l	48 h
	NOEC	Daphnia magna	0.0042 mg/l	21 d

Toxicity to aquatic plants

Components	End point	Species	Value	Exposure time
tetrasodium ethylene diamine tetraacetate	EC50	Desmodesmus subspicatus	1.01 mg/l	72 h
caustic soda	No data available			
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	NOEC static test Measured	Pseudokirchneriella subcapitata (green algae)	0.85 mg/l	72 h
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	EC50	Pseudokirchneriella subcapitata (green algae)	0.049 mg/l	72 h

12.2 Persistence and degradability

Component	Biodegradation	Exposure time	Summary
tetrasodium ethylene diamine tetraacetate	10 %	28 d	Not readily biodegradable.
caustic soda	No data available		

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide			Inherently biodegradable.
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	95.5 %	28 d	Readily biodegradable.

12.3 Bioaccumulative potential

Component	Bioconcentration factor (BCF)	Partition Coefficient n-Octanol/water (log)
tetrasodium ethylene diamine tetraacetate	1.8 Measured	-3.86
caustic soda	0.89 estimated	-1.38
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	71 QSAR	
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	79 Measured	3.91

12.4 Mobility in soil

Component	End point	Value
tetrasodium ethylene diamine tetraacetate	Koc	1046 estimated
caustic soda	No data available	
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	No data available	
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	Koc	1640329 Measured

12.5 Results of PBT and vPvB assessment

Component	Results
tetrasodium ethylene diamine tetraacetate	Not fulfilling PBT and vPvB criteria
caustic soda	Not fulfilling PBT and vPvB criteria
3-C12-18-(even numbered)-Alkylamido-N,N-dimethylpropan-1-amino oxide	Not fulfilling PBT and vPvB criteria
Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	Not fulfilling PBT and vPvB criteria

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3

Revision Date 06.11.2023

Print Date 06.11.2023

Specification Number: 350000043409

12.6 Endocrine Disrupting Properties

: The mixture does not contain any substances >0.1% that are included in the list established in accordance with Article 59(1) for having endocrine disrupting properties

12.7 Other adverse effects

: None known.

SECTION 13: DISPOSAL CONSIDERATIONS**13.1 Waste treatment methods**

Product

: Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with chemical or used container.

Packaging

: Do not re-use empty containers.

SECTION 14: TRANSPORT INFORMATION**Land transport**

Not classified as dangerous in the meaning of transport regulations.

Sea transport

Not classified as dangerous in the meaning of transport regulations.

Air transport

Not classified as dangerous in the meaning of transport regulations.

SECTION 15: REGULATORY INFORMATION**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

: This safety datasheet complies with the requirements of:

Regulation (EC) No. 1907/2006.

Regulation (EC) No. 1272/2008 (CLP) as amended (not applicable to cosmetics)

Regulation (EC) No. 528/2012 as amended (applicable to biocidal products)

Directive (EEC) No. 75/324 as amended (applicable to aerosols)

Regulation (EC) No. 1223/2009 amended (applicable to cosmetic products)

Regulation (EC) No. 684/2001 The surfactants contained in this preparation comply with the biodegradability criteria laid down in Regulation (EC) No.648/2004 for detergents (applicable to detergents).

Directive (EC) No. 2001/95/EC - General Product Safety Directive

SAFETY DATA SHEET

(Regulation (EU) 2020/878 amending the annex II of REACH regulation.)

**Janitol Original**

Version 1.3
Revision Date 06.11.2023

Print Date 06.11.2023
Specification Number: 350000043409

European Agreement concerning the International Carriage of Dangerous Goods by Road (ADR)

Directive 2012/18/EU Seveso

Regulation (EU) 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants.

SZW list of carcinogenic, mutagenic and reproductively toxic substances

15.2 Chemical safety assessment : Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the appropriate relevant information is incorporated into this Safety Data Sheet

SECTION 16: OTHER INFORMATION

If applicable, revision(s) are noted by the bold bars || in left-hand margin.

Key abbreviations or acronyms used

EC - European Community
EEC – European Economic Community
CLP – Classification Labelling & Packaging
EN – European Standard or European Norm
PBT – Persistent, Bioaccumulative & Toxic
vPvB – very persistent, very bioaccumulative
UN – United Nations

Evaluation methods

Unless otherwise stated in section 11, the procedure used to derive the human health classification is the relevant calculation method according to CLP regulation (EC) No 1272/2008 as amended.

Unless otherwise stated in section 12, the procedure used to derive the environmental classification is the summation of the classified components method according to CLP regulation (EC) No 1272/2008 as amended.

Full text of H-Statements

H302	Harmful if swallowed.
------	-----------------------

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.