


Bare Conductive Light Up Board Technical Data Sheet


PRODUCT DESCRIPTION

The Light Up Board is a touch-controlled, dimmable LED light on a 0.8mm thin circular PCB, which has six white LEDs and six gold-plated sensor electrodes. With it you can choose between touch, dimmer or proximity interaction modes and no computer programming is required. The Light Up Board uses the same MPR121 capacitive sensing chip as the Touch Board but it is even easier to use.

Quickly add light in a difficult to reach spot, demo a lighting control concept, or prototype a design for an interactive lamp. The Light Up Board is easy to use and is simple to integrate. Use our patent-pending twist and lock methody to attach the board to card or plastic, or stick it where you need it using double-sided tape or adhesive.

The Light Up Board also has a realistic candle light, spin and dice mode. To expand your creative possibilities still further, you can combine a Light Up Board with Electric Paint and other conductive materials. The Light Up Board is Micro-USB-powered by most phone-chargers or power banks, so you can wire it up permanently, or make it portable.





SUMMARY	
Microcontroller	Microchip ATmega88
• Touch IC	Resurgent Semiconductor MPR121
Input voltage	4.40V DC – 5.25V DC via MicroUSB connector
Current Consumption	200mA max (protected by 350mA PTC resettable fuse)
Operating voltage	3.3V DC
Capacitive touch electrodes	6
Flash memory	8kB
• SRAM	1kB
• EEPROM	512B
Clock speed	8MHz