


Metal (illuminated)selector




- ⊙ Φ 19mm diameter
- ⊙ Switch Rating: 5A/250VAC
- ⊙ Contact Configuration: 1NO1NC / 2NO 2NC
- ⊙ Two Position Remain / Three Position Remain
- ⊙ The crust material: Stainless Steel
- ⊙ Arrowhead Illuminated
- ⊙ IP Degree: IP67



Metal keylock switch



- ⊙ Φ 19mm diameter
- ⊙ Switch Rating: 5A/250VAC
- ⊙ Contact Configuration: 1NO1NC / 2NO 2NC
- ⊙ Two Position Remain / Three Position Remain
- ⊙ The crust material: Stainless Steel
- ⊙ IP Degree: IP65



Specification		LAS1-AGQ-□X/◆●/△/▲	LAS1-AGQ-□Y/◆●
The Front Shape		Selector	Key Lock
Terminal Type		Pin Terminal(2.8×0.5mm)	Pin Terminal(2.8×0.5mm)
Switching		No.3	No.3
Max.Switch Rating		Ith:5A Ui:250VAC	Ith:5A Ui:250VAC
Contact Resistance		≤50mΩ	≤50mΩ
Insulation Resistance		≥1000MΩ	≥1000MΩ
Dielectric Intensity		2000VAC	2000VAC
Operating Temp		-20℃ ~ +55℃	-20℃ ~ +55℃
Mechanical life		500,000cycles	500,000cycles
Electrical life		50,000cycles	50,000cycles
Panel Thickness		1 ~ 10mm	1 ~ 10mm
Torque		5 ~ 14Nm	5 ~ 14Nm
IP Degree		IP67	IP65
Material	Contact	Silver Alloy	Silver Alloy
	Button	Stainless Steel	Stainless Steel
	Body	Stainless Steel	Stainless Steel
	Base	PBT	PBT
LED Spec.	RoHS	Made to order	Made to order
	Type	Arrowhead(LED)	—
	Rated Voltage	6V / 12V / 24V / 110V / 220V	—
	Color	R G Y O B W	—
	Life	40000 hours	—
LAS1-AGQ State chart in operation	Position	Contact	Left Center Right
	90° Two position	1NO1NC	Left Contact C Right Contact C
		2NO2NC	Left Contact C Right Contact C
	45° 3 Three position	2NO2NC	Left Contact C Right Contact C