







Rating	21A 14VDC	Mounting Hole	Circuit Diagram									
Contact Resistance	50m ohm Max.											
Insulation Resistance	DC 500V 100M ohm Min.											
Dielectric Strength	AC 1500V 1 minute											
Operation Temperature	-25°~85°											
Switch Function	4P SPDT ON-OFF-ON	<table border="1"> <thead> <tr> <th>Thickness(mm)</th> <th>X(mm)</th> <th>Y(mm)</th> </tr> </thead> <tbody> <tr> <td>0.75-1.25</td> <td rowspan="3">21.2±0.1</td> <td>36.6±0.1</td> </tr> <tr> <td>1.25-2.0</td> <td>36.8±0.1</td> </tr> <tr> <td>2.0-3.0</td> <td>37.0±0.1</td> </tr> </tbody> </table>	Thickness(mm)	X(mm)	Y(mm)	0.75-1.25	21.2±0.1	36.6±0.1	1.25-2.0	36.8±0.1	2.0-3.0	37.0±0.1
Thickness(mm)	X(mm)	Y(mm)										
0.75-1.25	21.2±0.1	36.6±0.1										
1.25-2.0		36.8±0.1										
2.0-3.0		37.0±0.1										






Material:

1. Frame: Nylon-66(94V-2)
2. Actuator: Nylon-66+33%GF
- Len: PC
- Terminal: Silver plated copper
(excepted lamp terminal)
- Printed: None
2. Water proof: "IP-67"



TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

								△
								△
Date	Name	Description						NO
Drawn	Checked	Approved	SCI BOM No.		Model Name	ROCKER SWITCH		
C.J.Chan			Customer No.		Model No.	R13-292D3-BBRG-12D00 REV.		
03/27/09		6/109	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.			X