



APC Symmetra PX 48kW All-In-One Frame, 400V

Brand : APC

Product code: SYCF48KH

Product name : APC Symmetra PX 48kW All-In-One Frame, 400V

APC Symmetra PX 48kW All-In-One Frame, 400V

[APC Symmetra PX 48kW All-In-One Frame, 400V:](#)

Modular, high-efficiency 3-phase UPS that is scalable as your data center grows up to 160 kW/160 kVA. Suitable for small, medium & large data centers applications.

APC Symmetra PX 48kW All-In-One Frame, 400V. UPS topology: Double-conversion (Online), Output power capacity: 48 kVA, Output power: 48000 W. Serial interface type: RS-232. Battery technology: Sealed Lead Acid (VRLA), Battery capacity: 13824 VAh, Battery recharge time: 3 h. Form factor: Tower, Product colour: Black, Grey. Certification: EN 50091-1, EN/IEC 62040-1-1, EN/IEC 62040-2, EN/IEC 62040-3, Eurobat General Purpose, ISO 14001,...



Features		Battery	
UPS topology *	Double-conversion (Online)	Number of batteries supported	4
Output power capacity *	48 kVA	Battery recharge time	3 h
Output power *	48000 W	Hot-swap battery	✓
Waveform *	Sine	Design	
Input operation voltage (max) *	400 V	Form factor *	Tower
Input frequency *	40/70 Hz	Product colour *	Black, Grey
Output operation voltage (min)	230 V	Operational conditions	
Output operation voltage (max)	400 V	Operating temperature (T-T)	0 - 40 °C
Output frequency	50/60 Hz	Storage temperature (T-T)	-15 - 40 °C
Maximum current	98 A	Operating relative humidity (H-H)	0 - 95%
Number of input phases	3	Storage relative humidity (H-H)	0 - 95%
Number of output phases	3	Operating altitude	0 - 999.9 m
Three-phase input voltage supported	380,400,415 V	Non-operating altitude	0 - 15000 m
Three-phase output voltage supported	380,400,415 V	Certificates	
Output voltage Total Harmonic Distortion (THD)	2%	Certification	EN 50091-1, EN/IEC 62040-1-1, EN/IEC 62040-2, EN/IEC 62040-3, Eurobat General Purpose, ISO 14001, ISO 9001, VFI-SS-111
Noise level	61 dB	Weight & dimensions	
Ports & interfaces		Width	600 mm
Serial interface	✓	Depth	1070 mm
Serial interface type	RS-232	Height	1991 mm
Serial ports quantity	2	Weight	796 kg
Battery		Logistics data	
Battery technology	Sealed Lead Acid (VRLA)	Harmonized System (HS) code	85078000
Battery capacity	13824 VAh	Total carbon footprint (kg of CO2e)	1004.35



7612205026858

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.