



APC Symmetra RM 2kVA Scalable to 6kVA N+1 220-240V

Brand : APC

Product code: SYH2K6RMI

Product name : Symmetra RM 2kVA Scalable to 6kVA N+1 220-240V



Symmetra RM 2kVA Scalable to 6kVA N+1 220-240V

APC Symmetra RM 2kVA Scalable to 6kVA N+1 220-240V:

This parts kit contains spare parts for the APC product model shown.

APC Symmetra RM 2kVA Scalable to 6kVA N+1 220-240V. Output power capacity: 2 kVA, Output power: 1400 W. AC outlet types: NEMA L5-20R. Typical backup time at full load: 12.6 min, Typical backup time at half load: 29.8 min, Replacement battery cartridge: APC Replacement Battery SYBT2. Product colour: Black. Bundled software: - PowerChute Network Shutdown - PowerChute plus for AIX v4.2.3 - PowerChute plus for HP-UX v 4.2.3 - PowerChute plus for Linux v 4.5.2 - PowerChute plus for Novell NetWare v4.3.3 - PowerChute plus for Red Hat Linux v 4.5.2.1 - PowerChute plus for Solaris v 4.5 - PowerChute Plus for Windows NT/2000 (English) v. 5.2.1

Features		Operational conditions	
Output power capacity *	2 kVA	Storage relative humidity (H-H)	0 - 95%
Output power *	1400 W	Packaging data	
Emergency Power Off (EPO)	✓		
Ports & interfaces		Bundled software	- PowerChute Network Shutdown - PowerChute plus for AIX v4.2.3 - PowerChute plus for HP-UX v 4.2.3 - PowerChute plus for Linux v 4.5.2 - PowerChute plus for Novell NetWare v4.3.3 - PowerChute plus for Red Hat Linux v 4.5.2.1 - PowerChute plus for Solaris v 4.5 - PowerChute Plus for Windows NT/2000 (English) v. 5.2.1
AC outlet types	NEMA L5-20R		
Battery			
Typical backup time at full load	12.6 min		
Typical backup time at half load	29.8 min		
Replacement battery cartridge	APC Replacement Battery SYBT2		
Design		Logistics data	
Product colour *	Black	Harmonized System (HS) code	85078000
Operational conditions		Other features	
Operating temperature (T-T)	0 - 40 °C	Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte: leakproof
Storage temperature (T-T)	-15 - 45 °C	Interface	DB-9 RS-232, RJ-45 10 Base-T ethernet for web/ SNMP/ Telnet management
Operating relative humidity (H-H)	0 - 95%	Output connections	(8)IEC 320 C13 (2)IEC 320 C19
		Input connection type	Hard Wire 3-wire
		Dimensions (WxDxH)	482.6 x 730.3 x 355.6 mm
		Nominal output voltage	230 V
		Output voltage note	Configurable for 220: 230 or 240 nominal output voltage
		Nominal input voltage	230 V



8032976060445



5054444366470



8592978294533



3606485318684

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.