


Data Sheet

Primary Silver

V 364

Type Number..... 364
Designation IEC..... SR 60
System..... Silver oxide/ Zinc /
 NaOH - Electrolyte



Nominal Voltage..... 1,55 V
Typical Capacity C..... 20 mAh
 Load 39 kOhm, at 20°C down to 1.3 V

Weight (approx.)..... 0,33 g
Volume..... 0,07 ccm

Temperature Ranges min max.
 Storage..... -10°C 65°C
 Discharge..... -10°C 65°C

Dimensions min max.
 Diameter (A)..... 6,5 6,8
 Height (A/B)..... 1,9 2,15

Segment..... Watch

Main Applications..... Watch
 Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage: 1.3V
Continuous 24h/d, 7d/w Current [μ A]	39000 Ω 40	Time: 500 h Capacity [mAh]: 20 Energy [MWh]: 31

All Data contained herein is for single cells
 For battery applications, performance data may vary from single cell data, depending on specific battery configuration