PHILIPS

Philips V Line 221V8/00 computer monitor 54.6 cm (21.5") 1920 x 1080 pixels Full HD LED Black



Brand : Philips **Product family:** V Line **Product code:** 221V8/00

Product name : 221V8/00

- V Line
- 22 (21.5" / 54.6 cm diag.)
- Full HD (1920 x 1080)

221V8 LCD monitor



Philips V Line 221V8/00 computer monitor 54.6 cm (21.5") 1920 x 1080 pixels Full HD LED Black:

Philips V line wide-view monitor gives viewing beyond boundaries, great value with essential features. Adaptive-Sync provides flawless viewing without screen tearing. Features like LowBlue mode and flicker-free for easy-on-the eyes.
Philips V Line 221V8/00. Display diagonal: 54.6 cm (21.5"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. VESA mounting. Product colour: Black

Display	
Display diagonal *	54.6 cm (21.5")
Display resolution *	1920 x 1080 pixels
HD type *	Full HD
Native aspect ratio *	16:9
Display technology *	LED
Panel type *	VA
Backlight type	W-LED
Touchscreen *	✗
Display brightness (typical)	250 cd/m²
Response time *	4 ms
Screen shape *	Flat
Supported graphics resolutions	1280 x 720 (HD 720), 1920 x 1080 (HD 1080)
Supported video modes	720p, 1080p
Aspect ratio	16:9
Contrast ratio (typical) *	3000:1
Maximum refresh rate *	75 Hz
Viewing angle, horizontal	178°
Viewing angle, vertical	178°
Display number of colours *	16.7 million colours
Pixel pitch	0.24825 x 0.24825 mm
Pixel density	102 ppi
Horizontal scan range	30 - 85 kHz
Vertical scan range	48 - 75 Hz
Viewable size, horizontal	47.7 cm
Viewable size, vertical	26.8 cm
Digital horizontal frequency	30 - 85 kHz
Digital vertical frequency	48 - 75 Hz
Display diagonal (metric)	54.6 cm
DDC/CI	✔
Haze rate	25%

Ergonomics	
Tilt angle range	-5 - 20°
On Screen Display (OSD)	✔
On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Number of OSD languages	21
Plug and Play	✔
LED indicators	Operation, Stand-by

Power	
Energy efficiency class (SDR) *	E
Power consumption (typical) *	13.3 W
Power consumption (standby) *	0.5 W
Power consumption (off)	0.3 W
AC input voltage	100 - 240 V
AC input frequency	50 - 60 Hz
Power supply type	Internal

Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-20 - 60 °C
Operating relative humidity (H-H)	20 - 80%
Operating altitude	0 - 3658 m
Non-operating altitude	0 - 12192 m

Weight & dimensions	
Width (with stand)	493 mm
Depth (with stand)	220 mm
Height (with stand)	376 mm
Weight (with stand)	2.58 kg

Display	
Surface hardness	3H
Colour gamut standard	sRGB
3D	✗
Display sRGB	✓

Performance	
NVIDIA G-SYNC *	✗
AMD FreeSync *	✗
VESA Adaptive Sync support	✓
Component video sync	Separate Sync, Sync-on-green (SOG)
Flicker-free technology	✓
Low Blue Light technology	✓

Design	
Market positioning *	Home
Product colour *	Black

Ports & interfaces	
Built-in USB hub *	✗
VGA (D-Sub) ports quantity	1
DVI port	✗
HDMI *	✓
HDMI ports quantity	1
Audio input	✗
Audio output	✓
Headphone out *	✗

Ergonomics	
VESA mounting *	✓
Panel mounting interface	100 x 100 mm
Cable lock slot *	✓
Cable lock slot type	Kensington
Height adjustment *	✗
Tilt adjustment	✓

Weight & dimensions	
Width (without stand)	493 mm
Depth (without stand)	45 mm
Height (without stand)	294 mm
Weight (without stand)	2.2 kg

Packaging data	
Package width	565 mm
Package depth	111 mm
Package height	440 mm
Package weight	3.71 kg

Packaging content	
Stand included	✓
Cables included	HDMI, AC
Manual	✓

Sustainability	
Sustainability certificates	ENERGY STAR

Other features	
On/off switch	✓
Exterior finish type	Textured
Picture enhancement	SmartImage
Regulatory Approvals	CE Mark; CB; TUV/GS; TUV Ergo; CU-EAC; EPA; PSB; MEPS; RCM
Heavy metals free	Hg (mercury)
EasyRead mode	✓
LowBlue mode	✓
Energy efficiency class (old)	E
Compliance certificates	RoHS
Mean time between failures (MTBF)	50000 h
Certification	CE Mark, CB, TUV/GS, TUV Ergo, CU-EAC, EPA, PSB, MEPS, RCM

Recycling data	
Recyclable packaging material	100%

8712581760175

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date