



## APC GVSUPS10KB2HS uninterruptible power supply (UPS) Double-conversion (Online) 10 kVA 10000 W

**Brand :** APC

**Product code:** GVSUPS10KB2HS

**Product name :** GVSUPS10KB2HS

10 kVA, 10 kW, 40/70Hz, 55 dB, 333x847x1485mm, 245kg

APC GVSUPS10KB2HS uninterruptible power supply (UPS) Double-conversion (Online) 10 kVA 10000 W:


### GVSUPS10KB2HS Features

- Galaxy VS UPS 10kW 400V, 1 internal 7Ah smart modular battery string, expandable to 2, Start-up 5x8
- Highly efficient, easy-to-deploy 10kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and 1 smart high-capacity modular battery string, expandable to 2 strings for extended runtime.
- Includes: Battery modules ship installed, Dust filter, EcoStruxure Ready ((UPS)), Installation guide, Integrated network management, Power modules ship installed, Start-Up Service



| Features                                       |                            | Design                             |                                                                                                                                        |
|------------------------------------------------|----------------------------|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| UPS topology *                                 | Double-conversion (Online) | Form factor *                      | Tower                                                                                                                                  |
| Output power capacity *                        | 10 kVA                     | Product colour *                   | White                                                                                                                                  |
| Output power *                                 | 10000 W                    | Display type                       | LCD                                                                                                                                    |
| Waveform *                                     | Sine                       | International Protection (IP) code | IP20                                                                                                                                   |
| Input operation voltage (min) *                | 340 V                      | <b>Operational conditions</b>      |                                                                                                                                        |
| Input operation voltage (max) *                | 460 V                      | Operating temperature (T-T)        | 0 - 40 °C                                                                                                                              |
| Input frequency *                              | 40/70 Hz                   | Storage temperature (T-T)          | -15 - 40 °C                                                                                                                            |
| Output operation voltage (min)                 | 380 V                      | Operating relative humidity (H-H)  | 0 - 95%                                                                                                                                |
| Output operation voltage (max)                 | 415 V                      | Storage relative humidity (H-H)    | 10 - 80%                                                                                                                               |
| Output frequency                               | 50/60 Hz                   | Operating altitude                 | 0 - 1000 m                                                                                                                             |
| Maximum current                                | 18 A                       | Non-operating altitude             | 0 - 3000 m                                                                                                                             |
| Number of input phases                         | 3                          | <b>Certificates</b>                |                                                                                                                                        |
| Number of output phases                        | 3                          | Certification                      | CSA C22.2 NO. 107.3, EN/IEC 62040-1, EN/IEC 62040-2, EN/IEC 62040-3, FCC Part 15 Class A, IEC 60721-4-2 Level 2M2, UL 1778 5th edition |
| Input power factor                             | 0.99                       |                                    |                                                                                                                                        |
| Crest factor                                   | 2.5:1                      | <b>Packaging content</b>           |                                                                                                                                        |
| ECO mode                                       | ✓                          | Management card included           | ✓                                                                                                                                      |
| Output voltage Total Harmonic Distortion (THD) | 3%                         | Quick installation guide           | ✓                                                                                                                                      |
| Input current Total Harmonic Distortion (THD)  | 3%                         | <b>Weight &amp; dimensions</b>     |                                                                                                                                        |
| Noise level                                    | 55 dB                      | Width                              | 333 mm                                                                                                                                 |
| Power protection features                      | Overload, Short circuit    | Depth                              | 847 mm                                                                                                                                 |
| Audible alarm(s)                               | ✓                          |                                    |                                                                                                                                        |

| Ports & interfaces |                                                            | Weight & dimensions         |          |
|--------------------|------------------------------------------------------------|-----------------------------|----------|
| AC outlet types    | Hard Wire 4-wire (3PH + G), Hard Wire 5-wire (3PH + N + G) | Height                      | 1485 mm  |
| SmartSlot          | ✓                                                          | Weight                      | 245 kg   |
| SmartConnect port  | ✗                                                          | Packaging data              |          |
| Battery            |                                                            | Package width               | 640 mm   |
| Battery technology | Sealed Lead Acid (VRLA)                                    | Package depth               | 990 mm   |
| Battery voltage    | 480 V                                                      | Package height              | 1690 mm  |
|                    |                                                            | Package weight              | 270 kg   |
|                    |                                                            | Logistics data              |          |
|                    |                                                            | Harmonized System (HS) code | 85078000 |



0731304406709



731304406709

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.