

ASUS TUF Gaming VG279QL1A computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product family: TUF Gaming

Product code: 90LM05X0-B02170

Product name : VG279QL1A

- 27-inch Full HD (1920 x 1080) IPS gaming monitor with ultrafast 165*Hz refresh rate designed for professional gamers and immersive gameplay
 - ASUS Extreme Low Motion Blur (ELMB) technology eliminating ghosting and tearing for sharp gaming visuals with high frame rates
 - FreeSync™ Premium technology to eliminate screen tearing and choppy frame rates
 - G-SYNC Compatible, delivering a seamless, tear-free gaming experience by enabling VRR (variable refresh rate) by default
 - High Dynamic Range (HDR) technology with professional color gamut delivers contrast and color performance that meets the DisplayHDR™ 400 certification
- 27", 1920x1080, IPS, 400 cd/m², 1ms, 165Hz, HDR, HDCP, Flicker free, Low Blue Light, 2 x 2W RMS, 2 x HDMI, DisplayPort, 3.5mm, 614.09 x 364 x 56.95mm, 3.9 kg



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	HDMI version	2.0
Display resolution *	1920 x 1080 pixels	DisplayPorts quantity	1
HD type *	Full HD	DisplayPort version	1.2
Native aspect ratio *	16:9	Audio input	✗
Display technology *	LED	Headphone out *	✓
Panel type *	IPS	Headphone outputs	1
Touchscreen *	✗	Headphone connectivity	3.5 mm
Display brightness (typical)	400 cd/m²	HDCP	✓
Response time *	1 ms	Ergonomics	
Screen shape *	Flat	VESA mounting *	✓
Supported graphics resolutions	1920 x 1080 (HD 1080)	Panel mounting interface	100 x 100 mm
Aspect ratio	16:9	Cable lock slot *	✓
Contrast ratio (typical) *	1000:1	Cable lock slot type	Kensington
Maximum refresh rate *	165 Hz	Height adjustment *	✓
Viewing angle, horizontal	178°	Adjustable height (max)	12 cm
Viewing angle, vertical	178°	Pivot	✓
Display number of colours *	16.78 million colours	Pivot angle	-90 - 90°
Pixel pitch	0.311 x 0.311 mm	Swivelling	✓
Viewable size, horizontal	59.8 cm	Swivel angle range	-15 - 15°
Viewable size, vertical	33.6 cm	Tilt adjustment	✓
Viewable size diagonal	68.5 cm	Tilt angle range	-5 - 23°
Digital horizontal frequency	30 - 200 kHz	Power	
Digital vertical frequency	48 - 165 Hz	Energy efficiency class (SDR) *	F
High Dynamic Range (HDR) supported	✓	Energy consumption (SDR) per 1000 hours *	26 kWh
High Dynamic Range (HDR) technology	High Dynamic Range (HDR) 400	Power consumption (typical) *	18 W
DDC/CI	✓	Power consumption (off)	0.5 W
Colour gamut standard	sRGB	Power consumption (PowerSave)	0.5 W
sRGB coverage (typical)	125%	Energy efficiency scale	A to G

Performance		Weight & dimensions	
NVIDIA G-SYNC *	✓	Width (with stand)	614.1 mm
NVIDIA G-SYNC type	G-SYNC Compatible	Depth (with stand)	213.8 mm
AMD FreeSync *	✓	Height (with stand)	413.6 mm
AMD FreeSync type	FreeSync	Weight (with stand)	6.2 kg
VESA Adaptive Sync support	✓	Width (without stand)	614.1 mm
Flicker-free technology	✓	Depth (without stand)	59.6 mm
Low Blue Light technology	✓	Height (without stand)	364 mm
		Weight (without stand)	3.9 kg
Multimedia		Packaging data	
Number of speakers	2	Package width	730 mm
RMS rated power	2 W	Package depth	224 mm
Built-in speaker(s) *	✓	Package height	441 mm
Built-in camera *	✗	Package weight	9.5 kg
		Package type	Box
Design		Packaging content	
Market positioning *	Gaming	Stand included	✓
Product colour *	Black	Cables included	AC
Front bezel colour	Black	Quick start guide	✓
Detachable stand	✓		
Feet colour	Black		
Ports & interfaces		Other features	
Built-in USB hub *	✗	Certification	TUV Flicker-free , TUV Low Blue Light, VESA DisplayHDR 400
DVI port	✗		
HDMI *	✓	Logistics data	
HDMI ports quantity	2	Harmonized System (HS) code	85285210



4718017790086



0192876823712



192876823712

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.