



Lenovo EPYC AMD 7302 processor 3 GHz 128 MB L3 Tray

Brand : Lenovo

Product family: EPYC


Product code: 4XG7A38047

Product name : AMD EPYC 7302



16 Cores, 32 Threads, 3GHz, 3.3GHz Boost, 128MB L3 Cache, Socket SP3, 155W
Lenovo EPYC AMD 7302. Processor family: AMD EPYC, Processor socket: Socket SP3, Processor lithography: 7 nm. Memory channels: Octa-channel, Memory types supported by processor: DDR4-SDRAM, Memory clock speeds supported by processor: 3200 MHz. Market segment: Server


Processor		Memory	
Processor manufacturer *	AMD	Memory types supported by processor	DDR4-SDRAM
Processor model *	7302	Memory clock speeds supported by processor	3200 MHz
Processor base frequency *	3 GHz	Memory channels *	Octa-channel
Processor family *	AMD EPYC	Memory bandwidth (max)	204.8 GB/s
Processor cores *	16	Graphics	
Processor socket *	Socket SP3	On-board graphics card *	×
Component for	Server/workstation	Discrete graphics card *	×
Processor lithography *	7 nm	On-board graphics card model *	Not available
Processor threads	32	Discrete graphics card model *	Not available
Processor operating modes *	32-bit	Features	
Processor boost frequency	3.3 GHz	Market segment	Server
Processor cache	128 MB	Maximum number of PCI Express lanes	128
Processor cache type	L3	PCI Express slots version	4.0
Thermal Design Power (TDP)	155 W	Logistics data	
Package type *	Tray	Harmonized System (HS) code	85423119
Cooler included *	×		



0889488511877



889488511877



8894885118774

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.