

Philips E Line 322E1C/00 computer monitor 80 cm (31.5") 1920 x 1080 pixels Full HD LCD Black

Brand : Philips

Product family: E Line

Product code: 322E1C/00

Product name : 322E1C/00

322E1C Full HD Curved LCD display

Philips E Line 322E1C/00 computer monitor 80 cm (31.5") 1920 x 1080 pixels Full HD LCD Black:

The 32" curved E-Line display offers a truly immersive experience in a stylish design. Experience crisp Full HD visuals and smooth action with AMD FreeSync technology.
Philips E Line 322E1C/00. Display diagonal: 80 cm (31.5"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LCD, Display surface: Matt, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. VESA mounting. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	80 cm (31.5")	Audio output	✓
Display resolution *	1920 x 1080 pixels	Headphone out *	✗
HD type *	Full HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LCD	Panel mounting interface	100 x 100 mm
Panel type *	VA	Cable lock slot *	✓
LED backlight	✓	Cable lock slot type	Kensington
Backlight type	W-LED	Height adjustment *	✗
Touchscreen *	✗	Tilt adjustment	✓
Display brightness (typical)	250 cd/m²	Tilt angle range	-5 - 20°
Response time *	4 ms	On Screen Display (OSD)	✓
Response time measurement type	GTG (Gray to Gray)	On Screen Display (OSD) languages	Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
Display surface	Matt		
Anti-glare screen	✓		
Screen shape *	Curved	Number of OSD languages	21
Screen curvature rating	1500R	Plug and Play	✓
Supported graphics resolutions	1920 x 1080 (HD 1080)	LED indicators	Operation, Stand-by
Supported video modes	1080p	Power	
Aspect ratio	16:9	Energy efficiency class (SDR) *	F
Contrast ratio (typical) *	3000:1	Energy consumption (SDR) per 1000 hours *	27 kWh
Dynamic contrast ratio marketing name	Mega Infinity DCR	Power consumption (typical) *	40.6 W
Maximum refresh rate *	75 Hz	Power consumption (standby) *	0.5 W
Viewing angle, horizontal	178°	Power consumption (off)	0.3 W
Viewing angle, vertical	178°	AC input voltage	100 - 240 V
Display number of colours *	16.7 million colours		
Pixel pitch	0.364 x 0.364 mm		
Pixel density	70 ppi		
Horizontal scan range	53 - 84 kHz		

Display		Power	
Vertical scan range	48 - 75 Hz	AC input frequency	50/60 Hz
Viewable size, horizontal	69.8 cm	Power supply type	Internal
Viewable size, vertical	39.3 cm	Energy efficiency scale	A to G
Digital horizontal frequency	53 - 84 kHz	Operational conditions	
Digital vertical frequency	48 - 75 Hz	Operating temperature (T-T)	0 - 40 °C
Sync-on-green (SOG)	✓	Storage temperature (T-T)	-20 - 60 °C
Display diagonal (metric)	80 cm	Operating relative humidity (H-H)	20 - 80%
DDC/CI	✓	Operating altitude	0 - 3658 m
Haze rate	25%	Non-operating altitude	0 - 12192 m
Surface hardness	3H	Weight & dimensions	
Colour gamut standard	sRGB	Width (with stand)	709 mm
Colour gamut	85%	Depth (with stand)	281 mm
sRGB coverage (typical)	104%	Height (with stand)	523 mm
NTSC coverage (typical)	85%	Weight (with stand)	7.1 kg
3D	✗	Width (without stand)	709 mm
Separate H/V sync	✓	Depth (without stand)	88 mm
Display sRGB	✓	Height (without stand)	425 mm
Display panel size	31.5 inch/80 cm	Weight (without stand)	6.28 kg
Performance		Packaging data	
NVIDIA G-SYNC *	✗	Package width	800 mm
AMD FreeSync *	✓	Package depth	236 mm
AMD FreeSync type	FreeSync	Package height	625 mm
Component video sync	Separate Sync, Sync-on-green (SOG)	Package weight	10 kg
Flicker-free technology	✓	Package type	Box
Low Blue Light technology	✓	Packaging content	
Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1	Stand included	✓
Mac operating systems supported	✓	Cables included	HDMI, AC
		Manual	✓
Multimedia		Other features	
Built-in speaker(s) *	✗	Compatible operating systems	DDC/CI; Mac OS X; sRGB; Windows 10 / 8.1 / 8 / 7
Built-in camera *	✗	On/off switch	✓
Design		TV tuner integrated	✗
Market positioning *	Home	Exterior finish type	Textured
Product colour *	Black	Monitor sync input signal	Separate Sync; Sync on Green
Feet colour	Black	User controls	Power On/Off; Menu; Brightness; Input; SmartImage Game
Ports & interfaces		Picture enhancement	SmartImage game
Built-in USB hub *	✗	Signal input	VGA (Analogue); HDMI 1.4; DisplayPort 1.2
VGA (D-Sub) ports quantity	1	Regulatory Approvals	CE Mark; CU-EAC; CB; UKRAINIAN; TUV-BAUART
DVI port	✗	Heavy metals free	Hg (mercury)
HDMI *	✓	LowBlue mode	✓
HDMI ports quantity	1	Compliance certificates	CB, CE, EAC, RoHS, TÜV mark
HDMI version	1.4	Mean time between failures (MTBF)	50000 h
DisplayPorts quantity	1	Certification	CE Mark, CU-EAC, CB, UKRAINIAN, TUV-BAUART
DisplayPort version	1.2	Recycling data	
Audio input	✗	Total amount of recyclable materials	100%
		Recyclable packaging material	100%
		Logistics data	
		Harmonized System (HS) code	85285210



8712581758479

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.