



AOC V5 CU34V5CW computer monitor 86.4 cm (34") 3440 x 1440 pixels Wide Quad HD LED Black

Brand : AOC

Product family: V5

Product code: CU34V5CW/BK

Product name : CU34V5CW

Screen size (inch) 34, Panel resolution 3440x1440, Refresh rate 100 Hz, Response time MPRT 1 ms, Panel type VA, USB-C connectivity USB-C 3.2 x 1 (DP alt mode, upstream, power delivery up to 65 W), HDMI HDMI 2.0 x 1, Display Port DisplayPort 1.2 x 1, D-SUB (VGA) 0x, DVI 0x, Sync technology (VRR) Freesync

AOC V5 CU34V5CW computer monitor 86.4 cm (34") 3440 x 1440 pixels Wide Quad HD LED Black:

34" VA WQHD model for complex multitasking, with USB-C, MultiView and Windows Hello integrated webcam

The AOC CU34V5CW is a three-side frameless curved monitor equipped with a 34" VA panel with QHD UltraWide 21:9 resolution for an impressive and immersive viewing experience, ready to support any complex work with Picture by Picture MultiView. It offers a wide array of connectivity options thanks USB-C with Power Delivery up to 65W, 4 USB ports & HDMI. Log in easily and securely with Windows Hello integrated webcam.



Display		Ports & interfaces	
Display diagonal *	86.4 cm (34")	HDMI *	✓
Display resolution *	3440 x 1440 pixels	HDMI ports quantity	1
HD type *	Wide Quad HD	HDMI version	2.0
Native aspect ratio *	21:9	DisplayPorts quantity	1
Display technology *	LED	DisplayPort version	1.2
Panel type *	VA	Headphone out *	✓
LED backlight	✓	Headphone outputs	1
Backlight type	W-LED	Headphone connectivity	3.5 mm
Touchscreen *	✗	Built-in KVM switch	✗
Display brightness (typical)	300 cd/m²	AC (power) in	✓
Response time *	4 ms	Mobile High-Definition Link (MHL)	✗
Response time measurement type	GTG (Gray to Gray)		
Response time (MPRT)	1 ms		
Anti-glare screen	✓		
Screen shape *	Curved		
Screen curvature rating	1500R		
Contrast ratio (typical) *	3000:1		
Contrast ratio (dynamic)	20000000:1		
Maximum refresh rate *	100 Hz		
Viewing angle, horizontal	178°		
Viewing angle, vertical	178°		
Display number of colours *	16.7 million colours		
Pixel pitch	0.23175 x 0.23175 mm		
Pixel density	110 ppi		
Display diagonal (metric)	86.4 cm		
Surface hardness	6H		
Performance		Network	
NVIDIA G-SYNC *	✗	Ethernet LAN	✗
		Ergonomics	
		VESA mounting *	✓
		Panel mounting interface	100 x 100 mm
		Wall mountable	✓
		Cable lock slot *	✓
		Cable lock slot type	Kensington
		Height adjustment *	✓
		Adjustable height (max)	13 cm
		Pivot	✗
		Swivelling	✓
		Tilt adjustment	✓
		Tilt angle range	3 - 21°
		On Screen Display (OSD)	✓

Performance		Ergonomics	
AMD FreeSync *	✓	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Croatian, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Ukrainian
AMD FreeSync type	FreeSync		
Fast charging	✓		
Flicker-free technology	✓	Number of OSD languages	19
Low Blue Light technology	✓		
Multimedia		LED indicators	✓
Number of speakers	2	Power	
RMS rated power	10 W	Energy efficiency class (SDR) *	G
Built-in speaker(s) *	✓	Energy efficiency class (HDR) *	G
Megapixel (approx.)	2 MP	Energy consumption (SDR) per 1000 hours *	34 kWh
Built-in microphone	✗	Energy consumption (HDR) per 1000 hours *	35 kWh
Built-in camera *	✓	Power consumption (standby) *	0.5 W
Design		Power consumption (off)	0.3 W
Market positioning *	Home	AC input voltage	100 - 240 V
Product colour *	Black	AC input frequency	50/60 Hz
Frameless design	✓	Power supply type	Internal
Front bezel colour	Black	Energy efficiency scale	A to G
Detachable stand	✓	Packaging data	
Feet colour	Black	USB cable length	1.8 m
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Stand included	✓
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Cables included	AC, HDMI, USB Type-C
USB upstream port type	USB Type-C	HDMI cable length	1.5 m
Number of upstream ports	1	Other features	
Number of USB Type-C upstream ports quantity	1	Picture-by-Picture (PbP)	✓
USB Type-A downstream ports quantity	4	Exterior finish type	Matt
USB Type-C DisplayPort Alternate Mode	✓	Bezel thickness type	Frameless
USB Power Delivery (USB PD)	✓	Warranty period	3 year(s)
USB Power Delivery up to	65 W	Compliance certificates	CE
DVI port	✗	Mean time between failures (MTBF)	50000 h
		Light effects	✗
		Supplied AC adapter type	False
		Certification	CB,EAC



4038986110273

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.