

Philips S Line 275S9JAL/00 computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LCD Black

Brand : Philips

Product family: S Line

Product code: 275S9JAL/00

Product name : 275S9JAL/00

Business Monitor 275S9JAL LCD monitor

Philips S Line 275S9JAL/00 computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LCD Black:

Our S Line monitor delivers business efficiency. Features like Flicker-free and LowBlue mode make work easy on the eyes and increase your productivity.

Philips S Line 275S9JAL/00. Display diagonal: 68.6 cm (27"), Display resolution: 2560 x 1440 pixels, HD type: Quad HD, Display technology: LCD, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	HDCP version	1.4
Display resolution *	2560 x 1440 pixels	AC (power) in	✓
HD type *	Quad HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LCD	Panel mounting interface	100 x 100 mm
Panel type *	VA	Cable lock slot *	✓
Backlight type	W-LED	Cable lock slot type	Kensington
Touchscreen *	✗	Tilt adjustment	✓
Display brightness (typical)	300 cd/m²	Tilt angle range	-5 - 25°
Response time *	4 ms	On Screen Display (OSD)	✓
Anti-glare screen	✓	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Screen shape *	Flat		
Supported graphics resolutions	2560 x 1440		
Contrast ratio (typical) *	4000:1	Plug and Play	✓
Contrast ratio (dynamic)	50000000:1	LED indicators	Operation, Stand-by
Dynamic contrast ratio marketing name	SmartContrast	Power	
Maximum refresh rate *	75 Hz	Energy efficiency class (SDR) *	F
Viewing angle, horizontal	178°	Energy consumption (SDR) per 1000 hours *	26 kWh
Viewing angle, vertical	178°	Power consumption (typical) *	17.9 W
Display number of colours *	16.7 million colours	Power consumption (standby) *	0.3 W
Pixel pitch	0.2331 x 0.2331 mm	Power consumption (off)	0.3 W
Pixel density	108.79 ppi	Power consumption (PowerSave)	15.1 W
Horizontal scan range	30 - 114 kHz	AC input voltage	100 - 240 V
Vertical scan range	48 - 75 Hz	AC input frequency	50 - 60 Hz
Viewable size, horizontal	59.7 cm	Power supply type	Internal
Viewable size, vertical	33.6 cm		
Display diagonal (metric)	68.5 cm		
DDC/CI	✓		

Display		Power	
Haze rate	25%	Energy efficiency scale	A to G
Surface hardness	3H	Operational conditions	
Colour depth	8 bit	Operating temperature (T-T)	0 - 40 °C
sRGB coverage (typical)	119%	Storage temperature (T-T)	-20 - 60 °C
NTSC coverage (typical)	97%	Operating relative humidity (H-H)	20 - 80%
Display sRGB	✓	Operating altitude	0 - 3658 m
Performance		Non-operating altitude	0 - 12192 m
NVIDIA G-SYNC *	✗	Weight & dimensions	
AMD FreeSync *	✗	Width (with stand)	614 mm
Fast charging	✓	Depth (with stand)	226 mm
VESA Adaptive Sync support	✓	Height (with stand)	477 mm
Component video sync	Separate Sync	Weight (with stand)	5.1 kg
Flicker-free technology	✓	Width (without stand)	614 mm
Low Blue Light technology	✓	Depth (without stand)	55 mm
Multimedia		Height (without stand)	367 mm
Number of speakers	2	Weight (without stand)	4.46 kg
RMS rated power	4 W	Packaging data	
Built-in speaker(s) *	✓	Package width	690 mm
Built-in camera *	✗	Package depth	141 mm
Design		Package height	453 mm
Product colour *	Black	Package weight	7 kg
Frameless design	✓	Packaging content	
Front bezel colour	Black	Stand included	✓
Feet colour	Black	Cables included	HDMI, AC
Ports & interfaces		Manual	✓
Built-in USB hub *	✓	Bundled software	SmartControl
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Sustainability	
USB upstream port type	USB Type-B	Sustainability certificates	ENERGY STAR, TCO
Number of upstream ports	1	Doesn't contain	Mercury, PVC/BFR
Number of USB Type-B upstream ports quantity	1	Other features	
USB Type-A downstream ports quantity	2	Exterior finish type	Textured
HDMI *	✓	Picture enhancement	SmartImage
HDMI ports quantity	1	Regulatory Approvals	CB; CE Mark; CU-EAC; EAEU RoHS; FCC Class B; ICES-003; TUV Ergo; TUV/GS
HDMI version	1.4	EasyRead mode	✓
DisplayPorts quantity	1	LowBlue mode	✓
DisplayPort version	1.2	Compliance certificates	RoHS
Audio output	✓	Mean time between failures (MTBF)	70000 h
HDCP	✓	Recycling data	
		Recyclable packaging material	100%
		Post-consumer recycled plastic	85%



8712581796402

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.