



TP-Link 5G AX3000 Wi-Fi 6 Telephony Router

Brand : TP-Link

Product code: NX510V

Product name : 5G AX3000 Wi-Fi 6 Telephony Router

1 GHz Dual-Core CPU, 3× 10/100/1000 Mbps RJ45, 2.4/5 GHz, 802.11ax, 3G/4G/5G, 99 x 99 x 192mm
TP-Link 5G AX3000 Wi-Fi 6 Telephony Router. WAN connection type: RJ-45. Wi-Fi band: Dual-band (2.4 GHz / 5 GHz), Top Wi-Fi standard: Wi-Fi 6 (802.11ax), WLAN data transfer rate (max): 3000 Mbit/s.
Ethernet LAN interface type: Gigabit Ethernet, Ethernet LAN data rates: 10,100,1000 Mbit/s, Cabling technology: 10/100/1000Base-T(X). Mobile network generation: 5G, 3G standards: DC-HSDPA, HSDPA, HSPA+, HSUPA, WCDMA, 4G standard: LTE-TDD & LTE-FDD. Product type: Tabletop router, Product colour: White, LED indicators: LAN, LTE, Status



WAN connection		Security	
Ethernet WAN *	✓	Parental control	✓
DSL WAN *	✓	Design	
SIM card slot *	✓	Product colour	White
3G/4G USB modem compatibility *	✓	LED indicators	LAN, LTE, Status
WAN connection type	RJ-45	Product type *	Tabletop router
Wireless LAN features		Certificates	
Wi-Fi band *	Dual-band (2.4 GHz / 5 GHz)	Certification	CE, RoHS
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)	Packaging content	
WLAN data transfer rate (max) *	3000 Mbit/s	Cables included	LAN (RJ-45)
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax)	AC adapter included	✓
		Quick start guide	✓
WLAN data transfer rate (first band)	574 Mbit/s	Antenna	
WLAN data transfer rate (second band)	2402 Mbit/s	Antenna design *	Internal & external
Network		Features	
Ethernet LAN *	✓	Built-in processor	✓
Ethernet LAN interface type *	Gigabit Ethernet	Processor frequency	1000 MHz
Ethernet LAN data rates	10,100,1000 Mbit/s	Processor cores	2
Cabling technology	10/100/1000Base-T(X)	Power	
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11ax, IEEE 802.11g, IEEE 802.11k, IEEE 802.11n, IEEE 802.11r, IEEE 802.11v	Power source type *	AC
		AC input voltage	100 - 240 V
Port forwarding	✓	AC input frequency	50/60 Hz
Dynamic DNS (DDNS)	✓	Output voltage	12 V
Mobile network		Output current	2 A
Mobile network generation	5G	Operational conditions	
		Operating temperature (T-T)	0 - 40 °C

Mobile network		Operational conditions	
3G standards	DC-HSDPA, HSDPA, HSPA+, HSUPA, WCDMA	Storage temperature (T-T)	-40 - 70 °C
4G standard	LTE-TDD & LTE-FDD	Operating relative humidity (H-H)	10 - 90%
		Storage relative humidity (H-H)	5 - 90%
Ports & interfaces		Weight & dimensions	
Ethernet LAN (RJ-45) ports *	3	Width	99 mm
USB port *	✗	Depth	99 mm
DC-in jack	✓	Height	192 mm
Management features			
Quality of Service (QoS) support	✓		



4897098686874



4897098686867

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.