

StarTech.com DK31C3MNCRUE laptop dock/port replicator Wired USB 3.2 Gen 2 (3.1 Gen 2) Type-C

Brand : StarTech.com

Product code: DK31C3MNCRUE

Product name : DK31C3MNCRUE

StarTech.com USB-C Docking Station - Multi Monitor HDMI/DP/DP Alt Mode USB-C Dock - 3x 4K30 / 2x 4K60 - 7-Port USB Hub - 60W Power Delivery - GbE - 3.5mm Audio - Works With Chromebook certified - TAA

StarTech.com DK31C3MNCRUE. Connectivity technology: Wired, Host interface: USB 3.2 Gen 2 (3.1 Gen 2) Type-C, USB Power Delivery up to: 60 W. Ethernet LAN data rates: 10,100,1000 Mbit/s. Data transfer rate: 10 Gbit/s, HD type: 5K Ultra HD, Maximum digital resolution: 5120 x 2880 pixels. AC input voltage: 100 - 240 V, Input current: 2.37 A, Output voltage: 20 V. Width: 80 mm, Depth: 210 mm, Height: 32 mm



Ports & interfaces		Performance	
Connectivity technology *	Wired	Cable lock slot	✓
Host interface *	USB 3.2 Gen 2 (3.1 Gen 2) Type-C	Cable lock slot type	Kensington
USB 2.0 ports quantity *	2	LED indicators	Network, Power
USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity	3	Power	
USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity	1	AC input voltage	100 - 240 V
USB Power Delivery (USB PD)	✓	Input current	2.37 A
USB Power Delivery revision	3.0	Output voltage	20 V
USB Power Delivery up to	60 W	Output current	6.75 A
HDMI ports quantity *	2	Power consumption (typical)	135 W
HDMI version	2.0b	Compatible power plug types	EU, UK
DisplayPorts quantity	2	Wireless charging	✗
DisplayPort version	1.4	Operational conditions	
Combo headphone/mic port	✓	Operating temperature (T-T)	0 - 40 °C
Headphone outputs *	1	Storage temperature (T-T)	-20 - 70 °C
Headphone connectivity	3.5 mm	Operating relative humidity (H-H)	0 - 95%
DC-in jack	✓	Sustainability	
USB Type-C DisplayPort Alternate Mode	✓	Sustainability compliance	✓
Network		Weight & dimensions	
Ethernet LAN *	✓	Width	80 mm
Ethernet LAN (RJ-45) ports	1	Depth	210 mm
Ethernet LAN data rates	10,100,1000 Mbit/s	Height	32 mm
Performance		Packaging content	
Card reader integrated *	✗	Cables included	USB Type-C to USB Type-C
Data transfer rate	10 Gbit/s	AC adapter included	✓
HD type	5K Ultra HD	Quick start guide	✓

Performance		Technical details	
Maximum digital resolution	5120 x 2880 pixels	Compliance certificates	CE, RoHS
Maximum refresh rate	60 Hz	Other features	
		Chipset	Synaptics - VMM5320, Realtek - RTS5420, Parade - PS8469, Parade - PS8468, Parade - PS8805, Parade - PS8803, VIA/VLI - VL822 Realtek - ALC5686, VIA/VLI - VL211, Realtek - RTL8153B



0065030898133



065030898133

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.