

## DATA SHEET

## UNITRONIC® PUR CP

valid from :

24.06.2008

00328XX

## **Application**

UNITRONIC® PUR CP is a flexible, screened data cable with an outer sheath from PUR. The cable is suitable for fixed installation and flexible use, but not for highly flexible applications in power chains or permanently moved machines. The screen braiding protects against electrical interference. It may be used in dry, damp and wet rooms, also outdoor.

This data and signal cable is used in computer systems, electronic control and office equipment.

The outer sheath of Polyurethane is resistant to a multitude of oils and chemicals.

Design

Conductor fine-wire strands of bare copper wire; 0.14 mm<sup>2</sup> to 1.5 mm<sup>2</sup>, 7-wired for 0.34 mm<sup>2</sup>

Insulation PVC compound

Coding to DIN 47100

Stranding cores twisted in layers, wrapping by plastic foil

Screening braid of tinned copper, coverage approx. 85 %

Sheath PUR compound, grey (RAL 7032)

**Technical Data** 

Conductor resistance 0,14 mm $^2$  max. 148  $\Omega$ /km

0,25 mm<sup>2</sup> max. 79,9  $\Omega$ /km 0,34 mm<sup>2</sup> max. 57,5  $\Omega$ /km

0,5 mm<sup>2</sup> acc. to VDE 0295, Klasse 5 0,75 mm<sup>2</sup> acc. to VDE 0295, Klasse 5

Specific insulation resistance  $>20 \text{ G}\Omega \text{ x cm}$ 

Mutual capacitance at 800 Hz core/core ca. 120 nF/km core/screen ca. 160 nF/km

Inductance ca. 0,65 mH/km

Operating Voltage (not for power purposes) 250 V

Test voltage 0,14 mm<sup>2</sup>  $U_{eff}$  1200 V  $\geq$  0,25 mm<sup>2</sup>  $U_{eff}$  1500 V

Flame propagation flame retardant to IEC 60 332-1

Minimum bending radius static  $6 \times \emptyset$  cable moved  $15 \times \emptyset$  cable

oved 15 x Ø Cable

Temperature range static -5 bis +70 ℃

moved -30 bis +80 ℃

Design and electrical characteristics similar to Standard VDE 08122

**RoHS directive** This cabel confirms to RoHS directive (2002/95/EG)

elaborated by: TE-K:: P. Samek	Document:	DB0032800EN.doc	page 1 of 1
-----------------------------------	-----------	-----------------	-------------

Nr.: 0019/0894