

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINTOP® MS-XL</b>	<b>52115760</b> <b>14.11.2013</b>


Especially for thick walls  
Maximum reliability  
Wide, variable clamping ranges  
Optimum strain relief



Good chemical resistance



Mechanical resistance



Optimum strain relief



Robust



Temperature-resistant



Variety of approval certifications



### Application range

With long connection thread for applications involving a thicker wall.

### Design

PG connection thread

### Note

Counter nut to be used: SKINDICHT® SM

Refer to SKINTOP® PG accessories for suitable accessories

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MS-XL	1 / 3
--------------------	--------------------------	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINTOP® MS-XL</b>	<b>52115760</b> <b>14.11.2013</b>

#### Technical Data

Article designation / size:	MS 29 XL
Clamping range ØF (mm):	16 - 25
SW (mm):	40
Overall length, C (mm):	52
Thread length, D (mm):	15
Pieces / PU:	25
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	IP 68 - 5 bar
Temperature range:	-30°C to +100°C

Product Management	Document: SKINTOP® MS-XL	2 / 3
--------------------	--------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINTOP® MS-XL</b>	<b>52115760</b> <b>14.11.2013</b>



Product Management	Document: SKINTOP® MS-XL	3 / 3
--------------------	--------------------------	-------