



BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878
Issue date: 21/01/2022 Revision date: 01/10/2024 Version: 2.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : BIG ORANGE AUTOSHAMPOO
UFI : 1RUM-U3R0-M008-N0FJ
Product code : SDS-002-J-2.0
Type of product : Detergent

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses

Intended for general public
Main use category : Consumer use
Use of the substance/mixture : Automotive Care Products.

1.3. Details of the supplier of the safety data sheet

Turtle Wax Europe Limited
GB: Turtle Wax Europe Limited, Alaska House, Atlantic Park, Dunnings Bridge Road, Liverpool, L30 4AB.
EU: Turtle Wax EU B.V., WTC Schiphol Airport, D Tower, 11th Floor, Schiphol Boulevard 359, 1118 BJ, Amsterdam Schiphol, The Netherlands.
T : GB & EU +44 (0) 845 600 3663
MSDS@turtlewax.com

1.4. Emergency telephone number

Emergency number : GB & EU +44 (0) 845 600 3663
Office hours only 08:30 - 17:00

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation, Category 2 H319
Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

Causes serious eye irritation.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) : Warning
Hazard statements (CLP) : H319 - Causes serious eye irritation.
Precautionary statements (CLP) : P101 - If medical advice is needed, have product container or label at hand.
P102 - Keep out of reach of children.
P264 - Wash hands thoroughly after handling.
P280 - Wear eye protection.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 - If eye irritation persists: Get medical advice/attention.
EUH-statements : EUH208 - Contains BENZISOTHIAZOLINONE. May produce an allergic reaction.
Child-resistant fastening : Not applicable
Tactile warning : Not applicable

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

2.3. Other hazards

Other hazards which do not result in classification : None under normal conditions.

Contains no PBT and/or vPvB substances ≥ 0.1% assessed in accordance with REACH Annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or substance(s) are not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Benzisothiazolinone	CAS-No.: 2634-33-5 EC-No.: 220-120-9 EC Index-No.: 613-088-00-6	< 0.1	Acute Tox. 4 (Oral), H302 Acute Tox. 2 (Inhalation:dust,mist), H330 Skin Irrit. 2, H315 Eye Dam. 1, H318 Skin Sens. 1, H317 Aquatic Acute 1, H400 Aquatic Chronic 1, H410
acetic acid ... % substance with a Community workplace exposure limit (Note B)	CAS-No.: 64-19-7 EC-No.: 200-580-7 EC Index-No.: 607-002-00-6 REACH-no: 01-2119475328-30	< 0.1	Flam. Liq. 3, H226 Skin Corr. 1A, H314

Specific concentration limits:

Name	Product identifier	Specific concentration limits (%)
Benzisothiazolinone	CAS-No.: 2634-33-5 EC-No.: 220-120-9 EC Index-No.: 613-088-00-6	(0,036 ≤ C < 100) Skin Sens. 1; H317
acetic acid ... %	CAS-No.: 64-19-7 EC-No.: 200-580-7 EC Index-No.: 607-002-00-6 REACH-no: 01-2119475328-30	(10 ≤ C < 25) Eye Irrit. 2; H319 (10 ≤ C < 25) Skin Irrit. 2; H315 (25 ≤ C < 90) Skin Corr. 1B; H314 (90 ≤ C < 100) Skin Corr. 1A; H314

Note B: Some substances (acids, bases, etc.) are placed on the market in aqueous solutions at various concentrations and, therefore, these solutions require different classification and labelling since the hazards vary at different concentrations. In Part 3 entries with Note B have a general designation of the following type: 'nitric acid ... %'. In this case the supplier must state the percentage concentration of the solution on the label. Unless otherwise stated, it is assumed that the percentage concentration is calculated on a weight/weight basis.

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Not expected to present a significant hazard under anticipated conditions of normal use.
First-aid measures after skin contact	: Wash skin with plenty of water. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

First-aid measures after ingestion : Rinse mouth. Do not induce vomiting. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation : Not expected to present a significant inhalation hazard under anticipated conditions of normal use.

Symptoms/effects after skin contact : May cause an allergic skin reaction.

Symptoms/effects after eye contact : Causes serious eye irritation.

Symptoms/effects after ingestion : Ingestion may cause nausea, vomiting and diarrhea. May cause irritation to the digestive tract.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire.

5.2. Special hazards arising from the substance or mixture

Fire hazard : The product is not flammable.

Explosion hazard : Product is not explosive.

Reactivity in case of fire : Not known.

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Precautionary measures fire : Not applicable.

Firefighting instructions : Use extinguishing media appropriate for surrounding fire.

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Avoid release to the environment.

For non-emergency personnel

Protective equipment : Use personal protective equipment as required. For further information refer to section 8: "Exposure controls/personal protection".

Emergency procedures : Ventilate spillage area. Stop release. Do not touch or walk on the spilled product. Avoid contact with eyes.

For emergency responders

Protective equipment : Use personal protective equipment as required. For further information refer to section 8: "Exposure controls/personal protection".

Emergency procedures : Ventilate area. Stop release. Do not touch or walk on the spilled product. Avoid contact with eyes.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment : Collect spillage.

Methods for cleaning up : Wipe up with absorbent material (for example cloth). Place in a suitable container for disposal in accordance with the waste regulations (see Section 13). Wash away remainder with plenty of water. This material and its container must be disposed of in a safe way, and as per local legislation.

Other information : Dispose in a safe manner in accordance with local/national regulations.

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13 : "Disposal considerations".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Keep out of reach of children. Observe the label precautions. Use personal protective equipment as required. Avoid contact with eyes.
- Hygiene measures : Always wash hands after handling the product. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Store in a well-ventilated place. Keep cool. Keep out of reach of children. Protect against frost. Keep container closed when not in use.
- Storage area : Store in a well-ventilated place. Keep out of frost.
- Packaging materials : Keep only in original container.

7.3. Specific end use(s)

Automotive Care Products.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

National occupational exposure and biological limit values

acetic acid ... % (64-19-7)	
United Kingdom - Occupational Exposure Limits	
Local name	Acetic acid
WEL TWA (OEL TWA)	25 mg/m ³
	10 ppm
WEL STEL (OEL STEL)	50 mg/m ³
	20 ppm
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

8.2. Exposure controls

Appropriate engineering controls

Appropriate engineering controls:

Ensure adequate ventilation.

Personal protection equipment

Personal protective equipment:

In case of splash hazard: safety glasses.

Personal protective equipment symbol(s):



Eye and face protection

Eye protection:

Eye protection should only be necessary where liquid could be splashed or sprayed

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Skin protection

Skin and body protection:

Wear suitable protective clothing

Hand protection:

Protective gloves

Other skin protection

Materials for protective clothing:

Wear suitable working clothes

Respiratory protection

Respiratory protection:

Not required for normal conditions of use

Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

Consumer exposure controls:

Read label before use. Observe the label precautions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: dark orange.
Odour	: Citrus fruits.
Odour threshold	: Not available
Melting point	: Not available
Freezing point	: Not available
Boiling point	: Not available
Flammability	: Not applicable
Explosive properties	: Product is not explosive.
Oxidising properties	: Non oxidizing.
Lower explosion limit	: Not available
Upper explosion limit	: Not available
Flash point	: Not available
Auto-ignition temperature	: Not available
Decomposition temperature	: Not available
pH	: 6
Viscosity, kinematic	: Not available
Solubility	: Soluble in water.
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: Not available
Relative density	: 0.997 – 1.007
Relative vapour density at 20°C	: Not available
Particle characteristics	: Not applicable

9.2. Other information

Other safety characteristics

Refractive index : 1.3355 – 1.3375

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Acids. Oxidizing agent.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

Benzisothiazolinone (2634-33-5)

LD50 oral rat	450 mg/kg
LD50 dermal	4115 mg/kg bodyweight
LC50 Inhalation - Rat (Dust/Mist)	0.21 mg/l/4h

acetic acid ... % (64-19-7)

LD50 oral rat	3310 mg/kg bodyweight Animal: rat
LD50 oral	3310 mg/kg bodyweight

Skin corrosion/irritation : Not classified
pH: 6
Serious eye damage/irritation : Causes serious eye irritation.
pH: 6
Respiratory or skin sensitisation : Not classified
Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified
Reproductive toxicity : Not classified
STOT-single exposure : Not classified
STOT-repeated exposure : Not classified

acetic acid ... % (64-19-7)

NOAEL (oral, rat, 90 days)	290 mg/kg bodyweight Animal: rat, Animal sex: male
----------------------------	--

Aspiration hazard : Not classified

acetic acid ... % (64-19-7)

Viscosity, kinematic	1.015 mm²/s
----------------------	-------------

11.2. Information on other hazards

No additional information available

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Ecology - water	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified

Benzisothiazolinone (2634-33-5)

LC50 - Fish [1]	2.18 mg/l
EC50 - Crustacea [1]	0.99 mg/l
EC50 - Other aquatic organisms [1]	2.94 mg/l waterflea
EC50 - Other aquatic organisms [2]	0.11 mg/l

acetic acid ... % (64-19-7)

LC50 - Fish [1]	> 1000 mg/l
LC50 - Fish [2]	> 300.82 mg/l Test organisms (species): Oncorhynchus mykiss (previous name: Salmo gairdneri)
EC50 - Crustacea [1]	65 mg/l
EC50 - Crustacea [2]	> 300.82 mg/l Test organisms (species): Daphnia magna
EC50 - Other aquatic organisms [1]	> 1000 mg/l waterflea
EC50 72h - Algae [1]	> 1000 mg/l Test organisms (species): Skeletonema costatum
EC50 72h - Algae [2]	> 300.82 mg/l Test organisms (species): Skeletonema costatum

12.2. Persistence and degradability

BIG ORANGE AUTOSHAMPOO

Persistence and degradability	Not established.
-------------------------------	------------------

Benzisothiazolinone (2634-33-5)

Persistence and degradability	Not rapidly degradable
-------------------------------	------------------------

acetic acid ... % (64-19-7)

Persistence and degradability	Rapidly degradable
-------------------------------	--------------------

12.3. Bioaccumulative potential

BIG ORANGE AUTOSHAMPOO

Bioaccumulative potential	Not established.
---------------------------	------------------

Benzisothiazolinone (2634-33-5)

Partition coefficient n-octanol/water (Log Pow)	0.7
---	-----

acetic acid ... % (64-19-7)

Partition coefficient n-octanol/water (Log Pow)	-0.2
---	------

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

12.4. Mobility in soil

BIG ORANGE AUTOSHAMPOO

Ecology - soil	Not established.
----------------	------------------

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

Other adverse effects	: None known.
Additional information	: Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional waste regulation	: Disposal must be done according to official regulations.
Waste treatment methods	: Dispose of contents/container in accordance with licensed collector's sorting instructions.
Product/Packaging disposal recommendations	: Dispose in a safe manner in accordance with local/national regulations.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID number				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.2. UN proper shipping name				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard class(es)				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not applicable

Transport by sea

Not applicable

Air transport

Not applicable

Inland waterway transport

Not applicable

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Rail transport

Not applicable

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

Council Regulation (EC) for the control of dual-use items

Contains no substance subject to the COUNCIL REGULATION (EC) for the control of dual-use items

Detergent Regulation (648/2004)

Allergenic fragrances > 0.01 %:

BENZISOTHIAZOLINONE

LIMONENE

Labelling of contents	
Component	%
non-ionic surfactants, anionic surfactants	<5%
BENZISOTHIAZOLINONE	
perfumes	
LIMONENE	

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

BIG ORANGE AUTOSHAMPOO

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 16: Other information

Indication of changes:

Address Information. Regulatory information.

Full text of H- and EUH-statements:	
Acute Tox. 2 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 2
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment – Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment – Chronic Hazard, Category 1
EUH208	Contains BENZISOTHAZOLINONE. May produce an allergic reaction.
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
H226	Flammable liquid and vapour.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H330	Fatal if inhaled.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
Skin Corr. 1A	Skin corrosion/irritation, Category 1, Sub-Category 1A
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1

Safety Data Sheet (SDS), EU

Legal disclaimer: Turtle Wax Europe Limited. All rights reserved.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any particular conditions or process. Such information is, to the best of our knowledge and belief, accurate and reliable as of the date issued. No warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the responsibility of the user or processor to satisfy themselves as to the suitability of such information for their own particular circumstances, conditions or use. This includes transportation, storage and disposal which are outside of our control.