



A family company®

SAFETY DATA SHEET

Kresto® Citrus

This SDS is not mandated under the REACH etc. (Amendment etc.) (EU Exit) Regulations 2020 No. 1577 and is provided for information only.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Kresto® Citrus
Product number CIT2LT, CIT4LTR

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Hand cleaner.

1.3. Details of the supplier of the safety data sheet

Supplier SC Johnson Professional Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
+44 (0) 1773 855100
info.prouk@scj.com

1.4. Emergency telephone number

Emergency telephone Not Applicable Cosmetic Product

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (SI 2019 No. 720)

Physical hazards Not Classified
Health hazards Not Classified
Environmental hazards Not Classified

2.2. Label elements

Hazard statements NC Not Classified

Labelling notes This product is a cosmetic product regulated by and complying with Regulation EC No 1223/2009 (as amended) on Cosmetic Products in the EU/NI and in GB schedule 34 of the Product Safety and Metrology etc. (Amendment etc.) (EU Exit) Regulations 2019(as amended) and is thus exempt from the Safety Data Sheet requirements of EU & GB REACH. It is also exempt from the classification and labelling rules of the Classification, Labelling and Packaging Regulation.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Kresto® Citrus

| | |
|-------------|--|
| INCI | AQUA(WATER), TRIDECETH-10, ZEA MAYS (CORN) KERNEL MEAL, TRIDECETH-7, PARFUM (FRAGRANCE), SODIUM CARBOMER, PEG- 75 LANOLIN, TRITICUM VULGARE, 2-BROMO-2-NITROPROPANE-1,3-DIOL, LINALOOL, SIMMONDSIA CHINENSIS SEED OIL, MAGNESIUM NITRATE, MAGNESIUM CHLORIDE, METHYLCHLOROISOTHIAZOLINONE, METHYLISOTHIAZOLINONE |
|-------------|--|

SECTION 4: First aid measures

4.1. Description of first aid measures

| | |
|---------------------|---|
| Inhalation | Not relevant. Unlikely route of exposure as the product does not contain volatile substances. |
| Ingestion | Rinse mouth thoroughly with water. Get medical attention if any discomfort continues. |
| Skin contact | Not relevant. |
| Eye contact | Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention promptly if symptoms occur after washing. |

4.2. Most important symptoms and effects, both acute and delayed

| | |
|---------------------|-------------------------------------|
| Inhalation | No specific symptoms known. |
| Ingestion | No specific symptoms known. |
| Skin contact | No specific symptoms known. |
| Eye contact | May cause temporary eye irritation. |

4.3. Indication of any immediate medical attention and special treatment needed

| | |
|-----------------------------|------------------------------|
| Notes for the doctor | No specific recommendations. |
|-----------------------------|------------------------------|

SECTION 5: Firefighting measures

5.1. Extinguishing media

| | |
|-------------------------------------|---|
| Suitable extinguishing media | The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire. |
|-------------------------------------|---|

5.2. Special hazards arising from the substance or mixture

| | |
|--------------------------------------|--|
| Hazardous combustion products | No known hazardous decomposition products. |
|--------------------------------------|--|

5.3. Advice for firefighters

| | |
|---|---|
| Protective actions during firefighting | No specific firefighting precautions known. |
|---|---|

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

| | |
|-----------------------------|--------------------------|
| Personal precautions | Avoid contact with eyes. |
|-----------------------------|--------------------------|

6.2. Environmental precautions

| | |
|----------------------------------|---|
| Environmental precautions | Not considered to be a significant hazard due to the small quantities used. |
|----------------------------------|---|

6.3. Methods and material for containment and cleaning up

| | |
|--------------------------------|--|
| Methods for cleaning up | Flush away spillage with plenty of water. Avoid contamination of ponds or watercourses with washing down water. Absorb spillage with non-combustible, absorbent material. Do not discharge into drains or watercourses or onto the ground. |
|--------------------------------|--|

6.4. Reference to other sections

| | |
|------------------------------------|-------------------------------------|
| Reference to other sections | For waste disposal, see Section 13. |
|------------------------------------|-------------------------------------|

Kresto® Citrus

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid contact with eyes.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Stable at normal ambient temperatures.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Ingredient comments None.

8.2. Exposure controls

Appropriate engineering controls Not relevant.

Eye/face protection Not relevant.

Hygiene measures Not relevant.

Respiratory protection No specific recommendations.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance Viscous liquid.

Colour Beige.

Odour Lemon.

pH pH (concentrated solution): 6.5-7.5

9.2. Other information

Other information None.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None known.

10.4. Conditions to avoid

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

Kresto® Citrus

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General information A qualified toxicologist has evaluated and approved this product by conducting a Product Safety Assessment as per the Cosmetic Regulation n EC no 1223/2009 (as amended). Based on knowledge of the properties of the components, adverse effects on human health are not to be expected in normal use. Customer complaint data demonstrates the product to be completely harmless to the skin. The 48h Single Patch Test results show the product to be non-irritant.

Inhalation No specific health hazards known.

Ingestion May cause discomfort if swallowed.

Skin contact Skin irritation should not occur when used as recommended.

Eye contact May cause temporary eye irritation.

SECTION 12: Ecological information

Ecotoxicity Not regarded as dangerous for the environment.

12.1. Toxicity

12.2. Persistence and degradability

Persistence and degradability The surfactant(s) contained in this product complies(comply) with the biodegradability criteria as laid down in The Detergents Regulations (as amended).

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

12.4. Mobility in soil

Mobility The product is soluble in water.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information When handling waste, the safety precautions applying to handling of the product should be considered.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Reuse or recycle products wherever possible.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

Kresto® Citrus

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78

and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

This product is a cosmetic product regulated by and complying with Regulation EC No 1223/2009 (as amended) on Cosmetic Products in the EU/NI and in GB schedule 34 of the Product Safety and Metrology etc. (Amendment etc.) (EU Exit) Regulations 2019(as amended) and is thus exempt from the Safety Data Sheet requirements of EU & GB REACH. It is also exempt from the classification and labelling rules of the Classification, Labelling and Packaging Regulation.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

| | |
|--------------------------|----------------------|
| Revision comments | Product name change. |
| Revision date | 26/01/2022 |
| Revision | 11 |
| Supersedes date | 17/01/2019 |

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.