

Samsung VH55R-R LCD Indoor

Brand : Samsung

Product family: VMR-R

Product code:
LH55VMBRBGBXEN

Product name : VH55R-R

55", FHD (1920 x 1080), 500 cd/m², 1100:1, 24/7, 16:9, 72%, AC 100 - 240 V, 50/60 Hz, 270 W, 1211.0 x 681.7 x 69.9 mm
 Samsung VH55R-R. Display diagonal: 139.7 cm (55"), Display resolution: 1920 x 1080 pixels, Display technology: LCD, Display brightness: 500 cd/m², HD type: Full HD, Operating hours (hours/days): 24/7.
 Product colour: Black



Display		Ports & interfaces		
Display technology *	LCD	USB port	✓	
Display diagonal	139.7 cm (55")	USB ports quantity	1	
Display resolution	1920 x 1080 pixels	HDCP	✓	
HD type	Full HD	HDCP version	2.2	
Panel type	IPS	IR input ports quantity	1	
Pixel pitch *	0.63 x 0.63 mm	Audio input	✓	
Display brightness *	500 cd/m²	Audio output	✓	
Contrast ratio (typical)	1100:1			
Contrast ratio (dynamic)	500000:1	Power		
Response time	0.008 s	Power consumption (typical) *	270 W	
Viewing angle, horizontal	178°	Power consumption (sleep)	0.5 W	
Viewing angle, vertical	178°	Energy efficiency class (SDR)	G	
Horizontal scan range	57.3 - 70 kHz	Energy consumption (SDR) per 1000 hours	165 kWh	
Vertical scan range	47 - 63 Hz	AC input voltage	100 - 240 V	
Haze rate	28%	AC input frequency	50 - 60 Hz	
Colour gamut	72%			
Operating hours (hours/days)	24/7	Operational conditions		
Design		Operating temperature (T-T)	0 - 40 °C	
Placement supported *	Indoor	Operating relative humidity (H-H)	10 - 80%	
Orientation *	Horizontal/Vertical	Sustainability		
Bezel width (side)	0.44 mm	FCC (USA) Part 15, Subpart B Class A CE (Europe) : EN55022:2006+A1:2007 EN55024:1998+A1:2001+A2:2003 VCCI (Japan) : VCCI V-3 /2010.04 Class A KCC/EK (Korea) : Tuner : KN13 / KN20 Tunerless : KN22 / KN24 BSMI (Taiwan) : CNS13438 (ITE EMI) Class A / CNS13439 (AV EMI) / CNS14409 (AV EMS) / CNS14972 (Digital) C-Tick (Australia) : AS/NZS CISPR22:2009 CCC(China) : GB9254-2008 GB17625.1-2012 GOST(Russia/CIS) : GOST R 51317 Series, GOST 22505-97 EN55022:2006+A1:2007 EN55024:1998+A1:2001+A2:2003		
Bezel width (top)	0.44 mm			
Bezel width (bottom)	0.44 mm			
VESA mounting	✓			
Panel mounting interface	600 x 400 mm			
Product colour	Black			
Panel colour	Black			
Ports & interfaces				Certification
HDMI ports quantity	2			
HDMI version	2.0			
DVI port	✓			
DisplayPorts quantity	1			
DisplayPort version	1.2			
Ethernet LAN	✓			

Ports & interfaces		Weight & dimensions	
Ethernet LAN (RJ-45) ports	1	Width	1211 mm
RS-232 input ports	1	Depth	69.9 mm
RS-232 output ports	1	Height	681.7 mm
RS-232C	✓	Weight	16.8 kg
Packaging data			
		Package width	1414 mm
		Package depth	257 mm
		Package height	844 mm
		Package weight	25.1 kg



8806094282900

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.