SAMSUNG

Samsung LH82QPR8BCC Digital signage flat panel 2.08 m (82") LED Wi-Fi 500 cd/m² 8K Ultra HD Black 16/7



Brand : Samsung

Product code: LH82QPR8BCCXEN

Product name : LH82QPR8BCC

- Exceptional 8K resolution with 8K AI Upscaling technology
- Brilliant picture quality with QLED, 100% color volume and Quantum HDR
- Minimal and aesthetic design that enhances any customer environment

82", 7680 x 4320, Direct LED BLU, 500 cd/m², 1850:1, 6 ms, 16/7, Coretex A72 1.7 GHz, 2.5 GB LPDDR4, 8 GB, WiFi, Bluetooth, HDMI, USB, RJ45, RS232, WiFi, IR, 1835.0 x 1055.6 x 34.8 mm

Samsung LH82QPR8BCC. Product design: Digital signage flat panel. Display diagonal: 2.08 m (82"), Display technology: LED, Display resolution: 7680 x 4320 pixels, Display brightness: 500 cd/m², HD type: 8K Ultra HD. Wi-Fi. Operating hours (hours/days): 16/7. Product colour: Black



Display	
Display diagonal *	2.08 m (82")
Display technology *	LED
Display resolution *	7680 x 4320 pixels
Display brightness *	500 cd/m²
HD type *	8K Ultra HD
Touchscreen *	✗
Native aspect ratio	16:9
Response time	6 ms
Contrast ratio (typical)	1850:1
Dynamic contrast ratio marketing name	Mega Contrast
Viewing angle, horizontal	178°
Viewing angle, vertical	178°
Display number of colours	10.7 billion colours
Pixel pitch	78.36 x 235.08 mm

Ports & interfaces	
HDMI ports quantity *	4
HDMI input ports quantity	4
DVI port *	✗
USB port *	✓
USB ports quantity	3
Audio (L/R) out	1
RS-232C	✓

Audio	
Built-in speaker(s) *	✓
RMS rated power	60 W

Design	
Product design *	Digital signage flat panel
Placement supported *	Indoor
Orientation	Horizontal/Vertical
Product colour *	Black
VESA mounting *	✓

Design	
Panel mounting interface	600 x 400 mm

Performance	
Purpose *	Universal
Operating hours (hours/days)	16/7
HDCP	✓

Power	
Power consumption (standby) *	0.5 W
AC input voltage	100 - 240 V
AC input frequency	50 - 60 Hz

Computer system	
Computer system *	✓

Weight & dimensions	
Width	1835 mm
Depth	34.8 mm
Height	1055.6 mm
Weight	50 kg

Packaging data	
Package width	2039 mm
Package depth	260 mm
Package height	1224 mm
Package weight	70 kg

Packaging content	
Remote control included	✓
Cables included	AC

Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Operating relative humidity (H-H)	20 - 95%

Logistics data	
Harmonized System (HS) code	85285210

Network	
Ethernet LAN *	✔
Wi-Fi *	✔

8806090339851

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date