



## APC Back-UPS CS 325 w/o SW uninterruptible power supply (UPS) 0.325 kVA 210 W

**Brand :** APC

**Product code:** BK325I

**Product name :** Back-UPS CS 325 w/o SW

Back-UPS CS 325 w/o SW


APC Back-UPS CS 325 w/o SW uninterruptible power supply (UPS) 0.325 kVA 210 W:

APC Back-UPS CS, 210 Watts / 350 VA, Input 230V / Output 230V

APC Back-UPS CS 325 w/o SW. Output power capacity: 0.325 kVA, Output power: 210 W, Surge energy rating: 320 J. AC outlet types: IEC 60320. Battery technology: Sealed Lead Acid (VRLA), Battery recharge time: 6 h. Product colour: Beige. Certification: C-tick, CE, EN 50091-1, EN 50091-2, GOST, VDE



| Features                          |                         | Operational conditions          |                                               |
|-----------------------------------|-------------------------|---------------------------------|-----------------------------------------------|
| Output power capacity *           | 0.325 kVA               | Storage relative humidity (H-H) | 0 - 95%                                       |
| Output power *                    | 210 W                   | Certificates                    |                                               |
| Surge energy rating               | 320 J                   | Certification                   | C-tick, CE, EN 50091-1, EN 50091-2, GOST, VDE |
| Ports & interfaces                |                         | Packaging content               |                                               |
| AC outlet types                   | IEC 60320               | Management card included        | ✗                                             |
| Number of output IEC jumpers      | 3                       | Weight & dimensions             |                                               |
| SmartSlot                         | ✗                       | Weight                          | 5.73 kg                                       |
| SmartConnect port                 | ✗                       | Packaging data                  |                                               |
| Battery                           |                         | Package weight                  | 6.73 kg                                       |
| Battery technology                | Sealed Lead Acid (VRLA) | Logistics data                  |                                               |
| Battery recharge time             | 6 h                     | Harmonized System (HS) code     | 85078000                                      |
| Design                            |                         | Other features                  |                                               |
| Product colour *                  | Beige                   | Output connections              | IEC 320 C13                                   |
| Operational conditions            |                         | Input connection type           | IEC-320 C14                                   |
| Operating temperature (T-T)       | 0 - 40 °C               | Dimensions (WxDxH)              | 91 x 284 x 165 mm                             |
| Storage temperature (T-T)         | -15 - 45 °C             | Nominal output voltage          | 230 V                                         |
| Operating relative humidity (H-H) | 0 - 95%                 | Filtering description           | 5% IEEE                                       |
|                                   |                         | Nominal input voltage           | 230 V                                         |
|                                   |                         | Package dimensions (WxDxH)      | 241 x 368 x 178 mm                            |



0731304120506



731304120506



0132017967493



132017967493

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.