

ASUS PRIME H610M-K D4 Intel H610 LGA 1700 micro ATX


Brand : ASUS

Product code: 90MB1A10-M0EAY0

Product name : PRIME H610M-K D4



- Intel® LGA 1700 socket: Ready for 12th Gen Intel® processors
 - Comprehensive cooling: PCH heatsink and Fan Xpert
 - Ultrafast connectivity: 32Gbps M.2 slot, Realtek 1 Gb Ethernet and USB 3.2 Gen 1 support
 - 5X Protection III: Multiple hardware safeguards for all-round protection
 Intel® H610 (LGA 1700) mic-ATX motherboard with DDR4, PCIe 4.0, M.2 slot, Realtek 1 Gb Ethernet, HDMI®, D-Sub, USB 3.2 Gen 1 ports, SATA 6 Gbps, COM header, RGB header
 ASUS PRIME H610M-K D4. Processor manufacturer: Intel, Processor socket: LGA 1700, Compatible processor series: Intel® Celeron®, Intel® Core™ i3, Intel® Core™ i5, Intel® Core™ i7, Intel® Core™ i9,.... Supported memory types: DDR4-SDRAM, Maximum internal memory: 64 GB, Memory slots type: DIMM. Supported storage drive interfaces: M.2, SATA, Supported storage drive types: HDD & SSD, RAID levels: 0, 1, 5, 10. Ethernet interface type: Gigabit Ethernet. Component for: PC, Motherboard form factor: micro ATX, Motherboard chipset family: Intel



Processor		Rear panel I/O ports	
Processor manufacturer *	Intel	USB 2.0 ports quantity *	4
Processor socket *	LGA 1700	USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	2
Compatible processor series *	Intel® Celeron®, Intel® Core™ i3, Intel® Core™ i5, Intel® Core™ i7, Intel® Core™ i9, Intel® Pentium®, Intel® Pentium® Gold	Ethernet LAN (RJ-45) ports *	1
Maximum number of SMP processors	1	PS/2 ports quantity	1
Memory		VGA (D-Sub) ports quantity *	1
Supported memory types *	DDR4-SDRAM	HDMI ports quantity *	1
Number of memory slots *	2	HDMI version	2.1
Memory slots type	DIMM	Headphone outputs	1
Memory channels	Dual-channel	Microphone in	✓
ECC compatibility	Non-ECC	Network	
Supported memory clock speeds	2133,2400,2666,2800,2933,3000,3200 MHz	Ethernet LAN	✓
Maximum internal memory *	64 GB	Ethernet interface type	Gigabit Ethernet
Unbuffered memory	✓	Wi-Fi *	✗
Storage controllers		Features	
Supported storage drive types	HDD & SSD	Motherboard chipset *	Intel H610
Supported storage drive interfaces *	M.2, SATA	Audio output channels *	7.1 channels
RAID levels	0, 1, 5, 10	Component for *	PC
Graphics		Motherboard form factor *	micro ATX
Number of displays supported	2	Motherboard chipset family *	Intel
Internal I/O		Windows operating systems supported	Windows 10 x64, Windows 11 x64
USB 2.0 connectors *	1	Expansion slots	
USB 3.2 Gen 1 (3.1 Gen 1) connectors *	1	PCI Express x16 (Gen 3.x) slots	1
Number of SATA III connectors *	4	PCI Express x16 (Gen 4.x) slots	1
S/PDIF out connector	✓	Number of M.2 (M) slots	1
Front panel audio connector	✓	BIOS	
		BIOS type *	UEFI AMI
		BIOS memory size	128 Mbit

Internal I/O		Logistics data	
ATX Power connector (24-pin)	✓	Harmonized System (HS) code	84733020
CPU fan connector	✓	Weight & dimensions	
Number of chassis fan connectors	1	Width	234 mm
EPS power connector (8-pin)	✓	Depth	203 mm
Number of COM connectors	1	Height	51 mm
TPM connector	✓	Packaging content	
12V power connector	✓	Cables included	SATA
RGB LED pin header	✓	Drivers included	✓
		Other features	
		Weight	842 g



4711081565499



4711081565505

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.