APC Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19



Brand : APC

Product code: AP8459EU3

Product name : Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19

Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19

APC Rack PDU 2G, Metered-by-Outlet, ZeroU, 16A, 230V, (21) C13 & (3) C19:

APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection Current metering provides real-time remote monitoring of connected loads Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency

Design	
PDU types *	Metered, Metered-by-outlet
Rack capacity *	0U
Mounting	Vertical
Product colour	Black
Ports & interfaces	
AC outlets quantity *	24 AC outlet(s)
Power plug	IEC309
AC outlet types *	C13 coupler, C19 coupler
Output connections	21 x C13 & 3 x C19
Features	
LED indicators	✔
Cable length	3 m
Management features	
Monitoring	Current, Power, Voltage
Power	
Nominal input voltage *	200-230 V
AC input frequency	50 - 60 Hz
Maximum current *	16 A
Nominal output voltage	230 V
Load capacity	3680 VA
Maximum input current per phase	16 A
Maximum total current draw per phase	16 A
Maximum power	3680 W

Certificates	
Compliance certificates	RoHS
Certification	EN 55022 Class A, EN 55024, EN 61000-3-2, EN 61000-3-3, FCC Part 15 Class A, ICES-003, UL Listed, VCCI Class A, VDE REACH
Operational conditions	
Operating temperature (T-T)	-5 - 45 °C
Storage temperature (T-T)	-25 - 65 °C
Operating relative humidity (H-H)	5 - 95%
Storage relative humidity (H-H)	5 - 95%
Operating altitude	0 - 3000 m
Non-operating altitude	0 - 15000 m
Weight & dimensions	
Width	56 mm
Depth	51 mm
Height	1829 mm
Weight	6.76 kg
Packaging data	
Package weight	9.03 kg
Package width	163 mm
Package depth	117 mm
Package height	2037 mm
Logistics data	
Total carbon footprint (kg of CO2e)	4525.81

0731304317562

731304317562

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date