



Lenovo Xeon Intel Gold 6342 processor 2.8 GHz 36 MB

Brand : Lenovo

Product family: Xeon

Product code: 4XG7A63574

Product name : Intel Gold 6342

Intel Xeon Gold 6342 Processor (36M Cache, 2.80 GHz)

Lenovo Xeon Intel Gold 6342. Processor family: Intel® Xeon®, Processor socket: LGA 4189, Processor lithography: 10 nm. Memory channels: Octa-channel, Memory types supported by processor: DDR4-SDRAM. Market segment: Server, Supported instruction sets: SSE4.2, AVX, AVX 2.0, AVX-512, Scalability: 2S. Maximum Enclave Size Support for Intel® SGX: 64 GB. Processor package size: 77.5 x 56.5 mm

Processor		Processor special features	
Processor manufacturer *	Intel	Intel® Speed Shift Technology	✓
Processor generation	3rd Generation Intel® Xeon® Scalable	Intel® Transactional Synchronization Extensions	✓
Processor model *	6342	Intel® Total Memory Encryption	✓
Processor base frequency *	2.8 GHz	Intel® Crypto Acceleration	✓
Processor family *	Intel® Xeon®	Intel® Platform Firmware Resilience Support	✓
Processor cores *	24	Maximum Enclave Size Support for Intel® SGX	64 GB
Processor socket *	LGA 4189	Intel VT-x with Extended Page Tables (EPT)	✓
Component for	Server/workstation	Intel Software Guard Extensions (Intel SGX)	✓
Processor lithography *	10 nm	Intel 64	✓
Processor threads	48	Intel Virtualization Technology (VT-x)	✓
System bus rate	11.2 GT/s	Intel Virtualization Technology for Directed I/O (VT-d)	✓
Processor operating modes *	64-bit	AVX-512 Fused Multiply-Add (FMA) units	2
Processor boost frequency	3.5 GHz	Intel® Deep Learning Boost (Intel® DL Boost) on CPU	✓
Processor cache	36 MB	Intel® Resource Director Technology (Intel® RDT)	✓
Thermal Design Power (TDP)	230 W	Intel® Volume Management Device (VMD)	✓
Processor codename	Ice Lake	Intel® Run Sure Technology	✓
Memory		Mode-based Execute Control (MBE)	✓
Memory types supported by processor	DDR4-SDRAM	Intel® Optane™ DC Persistent Memory Supported	✓
Memory channels *	Octa-channel	Operational conditions	
ECC	✓	Tcase	81 °C
Graphics		Technical details	
On-board graphics card *	✗	Launch date	Q2'21
Discrete graphics card *	✗	Status	Launched
On-board graphics card model *	Not available	Supported memory types	DDR4-SDRAM
Discrete graphics card model *	Not available	Memory speed (max)	3200 MHz
Features		Number of UPI links	3
Execute Disable Bit	✓	Logistics data	
Market segment	Server	Harmonized System (HS) code	8542310001
Maximum number of PCI Express lanes	64	Weight & dimensions	
PCI Express slots version	4.0	Processor package size	77.5 x 56.5 mm
Supported instruction sets	SSE4.2, AVX, AVX 2.0, AVX-512	Other features	
Scalability	2S	Maximum internal memory	6 TB
Export Control Classification Number (ECCN)	5A992CN3		
Commodity Classification Automated Tracking System (CCATS)	G178966		
Processor special features			
Intel® Hyper Threading Technology (Intel® HT Technology)	✓		

Processor special features

Intel® Turbo Boost Technology	2.0
Intel® AES New Instructions (Intel® AES-NI)	✓
Intel Trusted Execution Technology	✓



0889488571857



889488571857

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.