

Epson WorkForce DS-1660W Flatbed scanner 1200 x 1200 DPI A4 Black, White



Brand : Epson

Product family: WorkForce

Product code: B11B244401PU

Product name : DS-1660W

1200x1200 DPI, ReadyScan LED, 25ppm, USB 3.0, Wireless LAN IEEE 802.11a/b/g/n, Wi-Fi Direct
Epson WorkForce DS-1660W. Maximum scan size: 210 x 3048 mm, Optical scanning resolution: 1200 x 1200 DPI, Enhanced scan resolution: 1200 x 1200 DPI. Scanner type: Flatbed scanner, Product colour: Black, White. Sensor type: CIS, Daily duty cycle (max): 1500 pages, Light source: ReadyScan LED. Auto document feeder (ADF) input capacity: 50 sheets. Maximum ISO A-series paper size: A4, ISO A-series sizes (A0...A9): A4, A5, A6, ISO B-series sizes (B0...B9): B5

Scanning		Ports & interfaces	
Maximum scan size *	210 x 3048 mm	USB port *	✓
Optical scanning resolution *	1200 x 1200 DPI	USB version	3.2 Gen 1 (3.1 Gen 1)
Enhanced scan resolution	1200 x 1200 DPI	Optional connectivity	Ethernet
Colour scanning	✓	Network	
Duplex scanning *	✓	Wi-Fi	✓
Input colour depth	30 bit	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n)
Output colour depth	24 bit	Ethernet LAN	✓
Input greyscale depth	10 bit	IPv6 support	✓
Output greyscale depth	8 bit	Supported network protocols	TCP/IP, DHCP, DNS, SNMP, SLP
ADF scan speed (b/w, A4)	25 ppm	Power	
ADF scan speed (colour, A4)	25 ppm	Power supply type *	AC
Design		Weight & dimensions	
Scanner type *	Flatbed scanner	Width	451 mm
Product colour *	Black, White	Depth	315 mm
Built-in display *	✗	Height	120 mm
Performance		Weight	3.9 kg
Sensor type *	CIS	Packaging data	
Light source	ReadyScan LED	Quantity per pack	1 pc(s)
Scan file formats	JPG, PDF, TIFF	Package width	195 mm
Daily duty cycle (max) *	1500 pages	Package depth	520 mm
Scan drivers	TWAIN	Package height	405 mm
Password protection	✓	Package weight	4.84 kg
Scanning noise level	55 dB	Packaging content	
Input capacity		Cables included	USB
Auto document feeder (ADF) input capacity	50 sheets	System requirements	
Paper handling		Windows operating systems supported	Windows 10, Windows 7, Windows 7 x64, Windows 8, Windows 8 x64, Windows 8.1, Windows 8.1 x64, Windows Vista, Windows Vista x64
Maximum ISO A-series paper size *	A4	Mac operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
ISO A-series sizes (A0...A9)	A4, A5, A6		
ISO B-series sizes (B0...B9)	B5		
Letter	✓		
Legal	✓		
Auto Document Feeder (ADF) media weight	50 - 120 g/m ²		
Maximum scan area (ADF)	210 x 3048 mm		

Paper handling		Operational conditions	
Minimum scan area (ADF)	89 x 127 mm	Operating temperature (T-T)	10 - 35 °C
		Storage temperature (T-T)	-20 - 80 °C
		Operating relative humidity (H-H)	20 - 80%
		Storage relative humidity (H-H)	20 - 80%
Logistics data			
		Harmonized System (HS) code	84716070



8715946672151

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.