Lenovo Xeon Intel Gold 5220R processor 2.2 GHz 35.75 MB



Brand : Lenovo **Product family:** Xeon **Product code:** 4XG7A37984

Product name : Intel Xeon Gold 5220R

Intel Xeon Gold 5220R 2.2GHz, 24C/48T, 10.4GT/s, 35.75M Cache, HT (150W) DDR4-2933

Lenovo Xeon Intel Gold 5220R processor 2.2 GHz 35.75 MB:

The Intel Xeon® 5220R 2.2GHz Twenty Four Core Processor enhances the performance and the speed of your system. Additionally, the Virtualization Technology enables migration of more environments. It supports enhanced SpeedStep® technology that allows tradeoffs to be made between performance and power consumption.

Its Thermal Monitoring Technologies protect the processor package and the system from thermal failure through several thermal management features. The VT-x with Extended Page Tables (EPT) also known as Second Level Address Translation (SLAT), provides acceleration for memory intensive virtualized applications. Packed with more features, the Xeon 5220R 2.2GHz Twenty Four Core Processor is the ideal choice for virtually all of your data demanding or standard enterprise infrastructure applications.

Processor	
Processor manufacturer *	Intel
Processor generation	2nd Generation Intel® Xeon® Scalable
Processor model *	5220R
Processor base frequency *	2.2 GHz
Processor family *	Intel® Xeon® Gold
Processor cores *	24
Processor socket *	LGA 3647 (Socket P)
Component for	Server/workstation
Processor lithography *	14 nm
Processor threads	48
Processor operating modes *	64-bit
Processor boost frequency	4 GHz
Processor cache	35.75 MB
Thermal Design Power (TDP)	150 W
Processor codename	Cascade Lake
Processor ARK ID	199354

Memory	
Maximum internal memory supported by processor	1 TB
Memory types supported by processor	DDR4-SDRAM
Memory clock speeds supported by processor	2667 MHz
Memory channels *	Hexa-channel
ECC	✔

Graphics	
On-board graphics card *	✘
Discrete graphics card *	✘
On-board graphics card model *	Not available
Discrete graphics card model *	Not available

Features	
Execute Disable Bit	✔
Market segment	Server
Maximum number of PCI Express lanes	48

Processor special features	
Intel® Hyper Threading Technology (Intel® HT Technology)	✔
Intel® Turbo Boost Technology	2.0
Intel® AES New Instructions (Intel® AES-NI)	✔
Enhanced Intel SpeedStep Technology	✔
Intel Trusted Execution Technology	✔
Intel® Speed Shift Technology	✔
Intel VT-x with Extended Page Tables (EPT)	✔
Intel 64	✔
Intel Virtualization Technology (VT-x)	✔
Intel Virtualization Technology for Directed I/O (VT-d)	✔
Intel Turbo Boost Max Technology 3.0	✘
AVX-512 Fused Multiply-Add (FMA) units	1
Intel® Deep Learning Boost (Intel® DL Boost) on CPU	✔
Intel® Speed Select technology - Performance Profile (Intel® SST-PP)	✘
Intel® Volume Management Device (VMD)	✔
Intel® Optane™ DC Persistent Memory Supported	✔
Intel® vPro™ Platform Eligibility	✔
Intel® Speed Select Technology - Base Frequency (Intel® SST-BF)	✘

Operational conditions	
Tcase	86 °C

Logistics data	
Harmonized System (HS) code	8542310001

Weight & dimensions	
Processor package size	76.0 x 56.5 mm

Features	
PCI Express slots version	3.0
Supported instruction sets	SSE4.2, AVX, AVX 2.0, AVX-512
Scalability	2S
Embedded options available	✕
PCI Express CEM revision	3.0



0889488507917



889488507917

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date