
Lenovo 4XC7A08248 network card Internal 100000 Mbit/s



Brand : Lenovo

Product code: 4XC7A08248

Product name : 4XC7A08248

Mellanox ConnectX-6 Dx 100GbE QSFP56 2-port PCIe 4 Ethernet Adapter


Lenovo 4XC7A08248 network card Internal 100000 Mbit/s:

The ThinkSystem Mellanox ConnectX-6 Dx 100GbE QSFP56 Ethernet Adapter is an advanced cloud Ethernet network adapter that accelerates mission-critical data-center applications such as security, virtualization, SDN/NFV, big data, machine learning, and storage.

This product guide provides essential presales information to understand the adapter and its key features, specifications, and compatibility. This guide is intended for technical specialists, sales specialists, sales engineers, IT architects, and other IT professionals who want to learn more about the ConnectX-6 Dx adapter and consider its use in IT solutions.
Lenovo 4XC7A08248. Internal. Connectivity technology: Wired, Host interface: PCI Express. Maximum data transfer rate: 100000 Mbit/s. Product colour: Black, Green, Stainless steel

Ports & interfaces	
Connectivity technology *	Wired
Host interface *	PCI Express
Fiber optic connector	QSFP56
Network	
Maximum data transfer rate *	100000 Mbit/s
Networking standards *	IEEE 802.1Q, IEEE 802.1Qaz, IEEE 802.1Qbb, IEEE 802.1Qbg, IEEE 802.3ad, IEEE 802.3ae, IEEE 802.3ap, IEEE 802.3az, IEEE 802.3ba, IEEE 802.3bj, IEEE 802.3by, IEEE 802.3cd
Design	
Component for *	Server

Design	
Product colour	Black, Green, Stainless steel
Internal *	✔
Certification	CB / cTUVus / CE EMC: CE / FCC / VCCI / ICES / RCM RoHS compliant
System requirements	
Windows operating systems supported	✔
Linux operating systems supported	✔



0889488525768



889488525768

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date