



AOC 24P3CW computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Black

Brand : AOC

Product code: 24P3CW

Product name : 24P3CW

Screen size (inch) 23.8, Panel resolution 1920x1080, Max Refresh rate 100 Hz, Panel type IPS, USB-C connectivity USB-C 3.2 x 1 (DP alt mode, upstream, power delivery up to 65 W), HDMI HDMI 1.4 x 1, DisplayPort DisplayPort 1.2 x 1 DisplayPort Out, Sync technology (VRR) Adaptive Sync AOC 24P3CW. Display diagonal: 60.5 cm (23.8"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	60.5 cm (23.8")	VESA mounting *	✓
Display resolution *	1920 x 1080 pixels	Panel mounting interface	100 x 100 mm
HD type *	Full HD	Wall mountable	✓
Native aspect ratio *	16:9	Cable lock slot *	✓
Display technology *	LED	Cable lock slot type	Kensington
Panel type *	IPS	Height adjustment *	✓
LED backlight	✓	Adjustable height (max)	15 cm
Backlight type	W-LED	Pivot	✓
Touchscreen *	✗	Pivot angle	-90 - 90°
Display brightness (typical)	300 cd/m ²	Swivelling	✓
Response time *	4 ms	Swivel angle range	180 - 180°
Response time measurement type	GTG (Gray to Gray)	Tilt adjustment	✓
Anti-glare screen	✓	Tilt angle range	-5 - 35°
Screen shape *	Flat	On Screen Display (OSD)	✓
Contrast ratio (typical) *	1000:1	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish
Contrast ratio (dynamic)	50000000:1		
Maximum refresh rate *	100 Hz	Number of OSD languages	16
Viewing angle, horizontal	178°	Power	
Viewing angle, vertical	178°	Energy efficiency class (SDR) *	E
Display number of colours *	16.7 million colours	Energy efficiency class (HDR) *	E
Pixel pitch	0.2745 x 0.2745 mm	Energy consumption (SDR) per 1000 hours *	18 kWh
Pixel density	93 ppi	Energy consumption (HDR) per 1000 hours *	18 kWh
Digital horizontal frequency	30 - 85 kHz	Power consumption (typical) *	14.5 W
Digital vertical frequency	48 - 75 Hz		
Display diagonal (metric)	60.5 cm		
High Dynamic Range (HDR) supported	✓		
Surface hardness	3H		
sRGB coverage (typical)	120.9%		

Display		Power	
Adobe RGB coverage	103%	Power consumption (standby) *	0.5 W
Performance		Power consumption (off)	0.3 W
Fast charging	✓	AC input voltage	100 - 240 V
Flicker-free technology	✓	AC input frequency	50/60 Hz
Low Blue Light technology	✓	Power supply type	Internal
Multimedia		Energy efficiency scale	A to G
		Weight & dimensions	
Number of speakers	2	Width (with stand)	540 mm
RMS rated power	10 W	Depth (with stand)	200.1 mm
Built-in speaker(s) *	✓	Height (with stand)	520.2 mm
Megapixel (approx.)	5 MP	Weight (with stand)	5.41 kg
Built-in microphone	✓	Width (without stand)	540 mm
Built-in camera *	✓	Depth (without stand)	50.7 mm
Design		Height (without stand)	343.6 mm
Market positioning *	Office	Weight (without stand)	3.7 kg
Product colour *	Black	Packaging data	
Frameless design	✓	Package width	613 mm
Front bezel colour	Black	Package depth	162 mm
Ports & interfaces		Package height	519 mm
Built-in USB hub *	✓	Package weight	7.56 kg
USB hub version	3.2 Gen 1 (3.1 Gen 1)	USB cable length	1.8 m
USB upstream port type	USB Type-C	Packaging content	
Number of upstream ports	1	Stand included	✓
Number of USB Type-C upstream ports quantity	1	Cables included	AC, HDMI, DisplayPort, USB Type-C
USB Type-A downstream ports quantity	4	DisplayPort cable length	1.8 m
USB Type-C DisplayPort Alternate Mode	✓	HDMI cable length	1.8 m
USB Power Delivery (USB PD)	✓	Power cable length	1.8 m
USB Power Delivery up to	65 W	Sustainability	
HDMI *	✓	Sustainability compliance	✓
HDMI ports quantity	1	Sustainability certificates	EPEAT Gold, TCO
HDMI version	1.4	Doesn't contain	Mercury, PVC/BFR
DisplayPorts quantity	1	Other features	
DisplayPort out quantity	1	Compatibility	VESA-P2
DisplayPort version	1.2	Local dimming	✓
Audio output	✓	Exterior finish type	Textured
Headphone out *	✓	Heavy metals free	Hg (mercury)
Headphone outputs	1	Bezel thickness type	Frameless
Headphone connectivity	3.5 mm	Warranty period	3 year(s)
HDCP	✓	Compliance certificates	CE
HDCP version	1.4	Mean time between failures (MTBF)	30000 h
Charging port type	USB Type-C	Certification	WEEE, REACH compliant, RoHs compliant, HF, CB, TUV-GS-Mark, ISO 9241-307, EAC, FCC
Network		Recycling data	
Ethernet LAN	✓	Recyclable packaging material	100%
		Post-consumer recycled plastic	85%



4038986140812

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.