



AOC V5 CU34V5C/BK computer monitor 86.4 cm (34") 3440 x 1440 pixels Wide Quad HD LED Black

Brand : AOC

Product family: V5

Product code: CU34V5C/BK

Product name : CU34V5C/BK

Screen size (inch) 34, Panel resolution 3440x1440, Refresh rate 100 Hz, Response time MPRT 1 ms, Panel type VA, USB-C connectivity USB-C 3.2 x 1 (DP alt mode, upstream, power delivery up to 65 W), HDMI HDMI 2.0 x 1, Display Port DisplayPort 1.2 x 1, D-SUB (VGA) 0x, DVI 0x, Sync technology (VRR) Freesync

AOC V5 CU34V5C/BK computer monitor 86.4 cm (34") 3440 x 1440 pixels Wide Quad HD LED Black:

34" VA WQHD panel for maximum productivity, with MultiView, USB-C and PD65W

The AOC CU34V5C is equipped with a 34" VA curved panel with Ultrawide QHD 21:9 resolution for an immersive viewing experience in a three-side frameless chassis that you can tilt and height adjust as needed. Ready to boost your productivity with USB-C with Power Delivery up to 65W, 4 USB ports & HDMI, it also offers Picture by Picture MultiView for the most complex multitasking.



Display		Ports & interfaces	
Display diagonal *	86.4 cm (34")	HDCP	✓
Display resolution *	3440 x 1440 pixels	HDCP version	2.2
HD type *	Wide Quad HD	AC (power) in	✓
Native aspect ratio *	21:9	Mobile High-Definition Link (MHL)	✗
Display technology *	LED	Network	
Panel type *	VA	Ethernet LAN	✗
LED backlight	✓	Ergonomics	
Backlight type	W-LED	VESA mounting *	✓
Touchscreen *	✗	Panel mounting interface	100 x 100 mm
Display brightness (typical)	300 cd/m²	Wall mountable	✓
Response time *	4 ms	Cable lock slot *	✓
Response time measurement type	GTG (Gray to Gray)	Cable lock slot type	Kensington
Response time (MPRT)	1 ms	Height adjustment *	✓
Anti-glare screen	✓	Adjustable height (max)	13 cm
Screen shape *	Curved	Pivot	✗
Screen curvature rating	1500R	Swivelling	✓
Contrast ratio (typical) *	3000:1	Tilt adjustment	✓
Contrast ratio (dynamic)	20000000:1	Tilt angle range	3 - 21°
Maximum refresh rate *	100 Hz	Picture-in-Picture	✓
Viewing angle, horizontal	178°	On Screen Display (OSD)	✓
Viewing angle, vertical	178°	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Croatian, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Ukrainian
Display number of colours *	16.7 million colours		
Pixel pitch	0.23175 x 0.23175 mm	Number of OSD languages	19
Pixel density	109.7 ppi		
Display diagonal (metric)	86.4 cm		
Surface hardness	6H		
sRGB coverage (typical)	116%		
NTSC coverage (typical)	101%		
Adobe RGB coverage	100%		

Display		Ergonomics	
DCI-P3 coverage	93%	LED indicators	✓
Performance		Power	
NVIDIA G-SYNC *	✗	Energy efficiency class (SDR) *	G
AMD FreeSync *	✓	Energy efficiency class (HDR) *	G
AMD FreeSync type	FreeSync	Energy consumption (SDR) per 1000 hours *	34 kWh
Fast charging	✓	Energy consumption (HDR) per 1000 hours *	35 kWh
Flicker-free technology	✓	Power consumption (typical) *	60 W
Low Blue Light technology	✓	Power consumption (standby) *	0.5 W
Multimedia		Power consumption (off)	0.3 W
Number of speakers	2	AC input voltage	100 - 240 V
RMS rated power	10 W	AC input frequency	50/60 Hz
Built-in speaker(s) *	✓	Power supply type	Internal
Built-in microphone	✗	Energy efficiency scale	A to G
Built-in camera *	✗	Weight & dimensions	
Design		Width (with stand)	808.1 mm
Market positioning *	Home	Depth (with stand)	250 mm
Product colour *	Black	Height (with stand)	527.3 mm
Frameless design	✓	Weight (with stand)	9.34 kg
Front bezel colour	Black	Width (without stand)	808.1 mm
Detachable stand	✓	Depth (without stand)	99.9 mm
Feet colour	Black	Height (without stand)	365.3 mm
Ports & interfaces		Weight (without stand)	6.76 kg
Built-in USB hub *	✓	Packaging data	
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package width	1071 mm
USB upstream port type	USB Type-C	Package depth	500 mm
Number of upstream ports	1	Package height	189 mm
Number of USB Type-C upstream ports quantity	1	Package weight	11.8 kg
USB Type-A downstream ports quantity	4	Package type	Box
USB Type-C DisplayPort Alternate Mode	✓	USB cable length	1.8 m
USB Power Delivery (USB PD)	✓	Packaging content	
USB Power Delivery up to	65 W	Stand included	✓
DVI port	✗	Cables included	AC, HDMI, USB Type-C
HDMI *	✓	HDMI cable length	1.5 m
HDMI ports quantity	1	Sustainability	
HDMI version	2.0	Doesn't contain	Mercury, PVC/BFR
DisplayPorts quantity	1	Other features	
DisplayPort version	1.2	Picture-by-Picture (PbP)	✓
Headphone out *	✓	Exterior finish type	Matt
Headphone outputs	1	Bezel thickness type	Frameless
Headphone connectivity	3.5 mm	Warranty period	3 year(s)
Built-in KVM switch	✗	Compliance certificates	CE
		Mean time between failures (MTBF)	50000 h
		Light effects	✗
		Supplied AC adapter type	False
		Certification	WEEE,REACH compliant,RoHs compliant,CB,TUV-Bauart-Mark,ISO 9241-307,EAC,FCC



4038986110198

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.