



AOC 24P3QW computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD Black

Brand : AOC

Product code: 24P3QW

Product name : 24P3QW

Screen size (inch) 23.8, Panel resolution 1920x1080, Max Refresh rate 100 Hz, Panel type IPS, HDMI HDMI 1.4 x 2, DisplayPort DisplayPort 1.2 x 1, Sync technology (VRR) Adaptive Sync

AOC 24P3QW computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD Black:

23.8" FHD flat IPS display for daily productivity in today's flexible office

The AOC 24P3QW is a 23.8" flat-screen IPS monitor with an attractive three-sided ultrathin bezel design that offers the features and performance you need to get the most out of every workday. With enhanced Full HD (1920 x 1080) resolution, 300-nit brightness, and generous 178/178° wide viewing angles, viewing is always a pleasure.

AOC 24P3QW. Display diagonal: 60.5 cm (23.8"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	60.5 cm (23.8")	Pivot angle	-90 - 90°
Display resolution *	1920 x 1080 pixels	Swivelling	✔
HD type *	Full HD	Swivel angle range	180 - 180°
Native aspect ratio *	16:9	Tilt adjustment	✔
Panel type *	IPS	Tilt angle range	-5 - 35°
LED backlight	✔	On Screen Display (OSD)	✔
Backlight type	W-LED	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish
Touchscreen *	✗		
Display brightness (typical)	300 cd/m²		
Response time *	4 ms		
Response time measurement type	GTG (Gray to Gray)		
Anti-glare screen	✔	Power	
Screen shape *	Flat	Energy efficiency class (SDR) *	D
Aspect ratio	16:9	Energy efficiency class (HDR) *	E
Contrast ratio (typical) *	1000:1	Energy consumption (SDR) per 1000 hours *	14 kWh
Contrast ratio (dynamic)	50000000:1	Energy consumption (HDR) per 1000 hours *	18 kWh
Maximum refresh rate *	100 Hz	Power consumption (typical) *	12.77 W
Viewing angle, horizontal	178°	Power consumption (standby) *	0.5 W
Viewing angle, vertical	178°	Power consumption (off)	0.3 W
Display number of colours *	16.7 million colours	AC input voltage	100 - 240 V
Pixel pitch	0.2745 x 0.2745 mm	AC input frequency	50/60 Hz
Pixel density	93 ppi	Power supply type	Internal
Digital horizontal frequency	30 - 85 kHz	Energy efficiency scale	A to G
Digital vertical frequency	48 - 100 Hz	Weight & dimensions	
Display diagonal (metric)	60.5 cm	Width (with stand)	540 mm
Surface hardness	3H	Depth (with stand)	200.1 mm
sRGB coverage (typical)	124.3%		

Performance		Weight & dimensions	
Fast charging	✓	Height (with stand)	520.2 mm
Flicker-free technology	✓	Weight (with stand)	5.06 kg
Low Blue Light technology	✓	Width (without stand)	540 mm
Multimedia		Depth (without stand)	50.7 mm
Number of speakers	2	Height (without stand)	326.3 mm
RMS rated power	10 W	Weight (without stand)	3.35 kg
Built-in speaker(s) *	✓	Packaging data	
Megapixel (approx.)	2 MP	Package width	613 mm
Built-in microphone	✓	Package depth	162 mm
Built-in camera *	✓	Package height	519 mm
Design		Package weight	8 kg
Market positioning *	Office	Packaging content	
Product colour *	Black	Stand included	✓
Front bezel colour	Black	Cables included	AC, HDMI, DisplayPort, USB
Detachable stand	✓	DisplayPort cable length	1.8 m
Ports & interfaces		HDMI cable length	1.8 m
Built-in USB hub *	✓	Power cable length	1.8 m
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Sustainability	
USB Type-A downstream ports quantity	4	Sustainability certificates	EPEAT Gold, TCO
HDMI *	✓	Doesn't contain	Mercury, PVC/BFR
HDMI ports quantity	2	Other features	
HDMI version	1.4	Compatibility	VESA-P2
DisplayPorts quantity	1	Local dimming	✓
DisplayPort version	1.2	Picture-by-Picture (PbP)	✓
Audio output	✓	Exterior finish type	Textured
HDCP	✓	Heavy metals free	Hg (mercury)
HDCP version	1.4	Bezel thickness type	Frameless
Ergonomics		Warranty period	3 year(s)
VESA mounting *	✓	Compliance certificates	CE
Panel mounting interface	100 x 100 mm	Mean time between failures (MTBF)	30000 h
Cable lock slot *	✓	Certification	WEEE, REACH compliant, RoHs compliant, HF, CB, TUV-GS-Mark, ISO 9241-307, EAC, FCC
Cable lock slot type	Kensington	Recycling data	
Height adjustment *	✓	Recyclable packaging material	100%
Adjustable height (max)	15 cm	Post-consumer recycled plastic	85%
Pivot	✓		



4038986140775

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.